

SAC-MS/50,0-94H/MS HYB SCO - Hybrid cable



1405673

<https://www.phoenixcontact.com/us/products/1405673>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled Ethernet cable, CAT5e, shielded, 8-pair, 26 AWG stranded (19-wire), RAL 9005 (black), M12 hybrid plug to M12 hybrid plug, length: 50.0 m

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1405673 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | AF1CML |
| GTIN | 4046356752978 |
| Weight per piece (including packing) | 4,431.3 g |
| Weight per piece (excluding packing) | 4,431.3 g |
| Country of origin | PL |

SAC-MS/50,0-94H/MS HYB SCO - Hybrid cable



1405673

<https://www.phoenixcontact.com/us/products/1405673>

Technical data

Product properties

| | |
|----------------------|-------------------------|
| Product type | Data cable preassembled |
| Sensor type | Ethernet |
| Number of positions | 8 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | Y |

Insulation characteristics

| | |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

Interfaces

| | |
|----------------------|--------------------------------|
| Bus system | Ethernet |
| Signal type/category | Ethernet CAT5 (IEC 11801:2002) |

Signaling

| | |
|----------------|----|
| Status display | no |
|----------------|----|

Electrical properties

| | |
|---|--------------------------|
| Nominal voltage U_N | 30 V AC (Power and data) |
| | 30 V DC |
| Nominal current I_N | 6 A (Power) |
| | 0.5 A (Data) |
| Transmission medium | Copper |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002) |

Material specifications

| | |
|--|------------------------------|
| Flammability rating according to UL 94 | V0 |
| Material for screw connection | Zinc die-cast, nickel-plated |

Connector

Connection 1

| | |
|----------------------|-----------------------------------|
| Type | Plug straight M12 SPEEDCON / IP65 |
| Number of positions | 8 (4+4) |
| Locking type | SPEEDCON |
| Coding type | Y (Hybrid) |
| Shielded | yes |
| Handle color | black |
| Degree of protection | IP65 |
| | IP67 |

Connection 2

SAC-MS/50,0-94H/MS HYB SCO - Hybrid cable



1405673


<https://www.phoenixcontact.com/us/products/1405673>

| | |
|----------------------|-----------------------------------|
| Type | Plug straight M12 SPEEDCON / IP65 |
| Number of positions | 8 (4+4) |
| Locking type | SPEEDCON |
| Coding type | Y (Hybrid) |
| Shielded | yes |
| Handle color | black |
| Degree of protection | IP65 |
| | IP65 |

Cable/line

| | |
|--------------|------|
| Cable length | 50 m |
|--------------|------|

Ethernet hybrid [94H]

| | |
|-------------------------------------|---|
| Dimensional drawing |  |
| Cable weight | 87 kg/km |
| UL AWM Style | 20963 (80°C/30 V) |
| Number of positions | 8 |
| Shielded | yes |
| Cable type | Ethernet hybrid [94H] |
| Conductor structure | 1x4xAWG26 + 1x4xAWG20 |
| Conductor structure signal line | 19x 0.10 mm |
| AWG signal line | 26 |
| Conductor structure, voltage supply | 19x 0.20 mm |
| AWG power supply | 20 |
| Conductor cross-section | 4x 0.15 mm ² (Data) 4x 0.6 mm ² (Power) |
| Wire diameter incl. insulation | 1.05 mm (Data) 1.4 mm (Power) |
| External cable diameter | 7.60 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | black RAL 9005 |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PP (Data) PP (Power) |
| Single wire, color | white/orange, orange, white/green, green, white, blue, brown, black |
| Overall twist | 1 star quad and 4 wires with 2 fillers |

SAC-MS/50,0-94H/MS HYB SCO - Hybrid cable



1405673

<https://www.phoenixcontact.com/us/products/1405673>

| | |
|---|--|
| Optical shield covering | 85 % |
| Insulation resistance | ≥ 5 GΩ*km |
| Loop resistance | ≤ 280.00 Ω/km (Data) |
| | ≤ 34.60 Ω/km (Power) |
| Wave impedance | 100 Ω ±15 Ω (4 MHz ... 100 MHz) |
| Working capacitance | nom. 50 nF (per kilometer) |
| Differential impedance | 100 Ω ±5 % (at 100 MHz) |
| Nominal voltage, cable | ≤ 50 V (Peak value, not for high-power applications) |
| Test voltage Core/Core | 1500 V (50 Hz, 1 min.) |
| Test voltage Core/Shield | 1500.00 V (50 Hz, 1 min.) |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 10 x D |
| Smallest bending radius, fixed installation | 38 mm |
| Smallest bending radius, movable installation | 76 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 2000000, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 4 m/s ² |
| Tensile strength | 70 N (in accordance with DIN EN 50565-1 for flexible installation) |
| | 240 N (in accordance with DIN EN 50565-1 for fixed installation) |
| Near end crosstalk attenuation (NEXT) | 56.3 dB (at 4 MHz) |
| | 50.3 dB (at 10 MHz) |
| | 47.2 dB (at 16 MHz) |
| | 45.8 dB (at 20 MHz) |
| | 42.9 dB (at 31.25 MHz) |
| | 38.4 dB (at 62.5 MHz) |
| | 35.3 dB (at 100 MHz) |
| Shield attenuation | 6 dB (at 4 MHz) |
| | 9.5 dB (at 10 MHz) |
| | 12.1 dB (at 16 MHz) |
| | 13.5 dB (at 20 MHz) |
| | 17.1 dB (at 31.25 MHz) |
| | 24.8 dB (at 62.5 MHz) |
| | 32 dB (at 100 MHz) |
| | ≥ 80.00 dB (30 MHz ... 125 MHz) |
| Halogen-free | according to IEC 60754 |
| | in accordance with DIN VDE 0472 part 815 |
| Flame resistance | in acc. with UL 1581, section 1061 |
| | in acc. with UL 1581, section 1061 |
| Resistance to oil | according to IEC 60811-2-1 |
| | according to VDE 0282 Part 10 |
| Other resistance | Low adhesion |
| Special properties | Free of substances which would hinder coating with paint or varnish |
| | Silicone-free |
| Ambient temperature (operation) | -40 °C ... 90 °C (cable, fixed installation) |

SAC-MS/50,0-94H/MS HYB SCO - Hybrid cable




1405673

<https://www.phoenixcontact.com/us/products/1405673>

-30 °C ... 70 °C (Cable, flexible installation)


Drawings

Dimensional drawing



M12 connector, straight, shielded

Schematic diagram



M12 hybrid connector pin assignment, 8-pos., pin side view

SAC-MS/50,0-94H/MS HYB SCO - Hybrid cable



1405673

<https://www.phoenixcontact.com/us/products/1405673>

Circuit diagram



SAC-MS/50,0-94H/MS HYB SCO - Hybrid cable



1405673

<https://www.phoenixcontact.com/us/products/1405673>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-MS/50,0-94H/MS HYB SCO - Hybrid cable



1405673

<https://www.phoenixcontact.com/us/products/1405673>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com