

# VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141

<https://www.phoenixcontact.com/us/products/1405141>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 4, CAT5 (IEC 11801:2002), material: Metal, connection method: IDC fast connection, connection cross section: AWG 26- 22, cable outlet: straight, color: silver, PROFINET

## Commercial data

Item number	1405141
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOAA
GTIN	4046356325929
Weight per piece (including packing)	70.5 g
Weight per piece (excluding packing)	70.5 g
Customs tariff number	85366990
Country of origin	DE

# VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141

<https://www.phoenixcontact.com/us/products/1405141>

## Technical data

### Product properties

Product type	Data connector (cable side)
Type	RJ45
Number of positions	4
Connection profile	RJ45 8(4)
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Nominal voltage $U_N$	48 V
Contact resistance	0.001 $\Omega$ (Wire – IDC)
	0.005 $\Omega$ (Litz wires – IDC)
Transmission medium	Copper
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

### Connection data

#### Connection technology

Connection method	IDC fast connection
Connection cross section AWG	26 ... 22 (solid)
	26 ... 22 (flexible)
Conductor cross-section	0.13 mm <sup>2</sup> ... 0.32 mm <sup>2</sup> (solid)
	0.14 mm <sup>2</sup> ... 0.36 mm <sup>2</sup> (flexible)

### Interfaces

Signal type/category	PROFINET CAT5 (IEC 11801:2002)
----------------------	--------------------------------

### Dimensions

Width	22 mm
Height	30 mm
Length	72 mm

### Material specifications

Color	silver
Material	Metal

# VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141

<https://www.phoenixcontact.com/us/products/1405141>

Flammability rating according to UL 94	V0
Seal material, O-ring	NBR
Seal material cable seal	TPE
Seal material	NBR
Housing material	Metal
Housing surface material	nickel-plated
Cable seal material	TPE
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
O-ring material	NBR
Material for screw connection	CuZn

## Cable/line

Signal type/category	PROFINET CAT5 (IEC 11801:2002)
External cable diameter	5 mm ... 8 mm
External cable diameter	5 mm ... 8 mm

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Ambient temperature (assembly)	-5 °C ... 45 °C

## Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

# VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector





1405141

<https://www.phoenixcontact.com/us/products/1405141>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405141>

 <b>cUL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
Only rigid conductors	50 V	1.75 A	- 22	-

 <b>UL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
Only rigid conductors	50 V	1.75 A	- 22	-

# VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141

<https://www.phoenixcontact.com/us/products/1405141>

## Classifications

### ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

### ETIM

ETIM 10.0	EC003083
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-PPC-C1-RJ45-MNNA-PG9-4Q5-B - RJ45 connector



1405141

<https://www.phoenixcontact.com/us/products/1405141>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) 2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	290a0695-ad91-4dda-acc9-838b8742ba2e

### EF3.1 Climate Change

CO2e kg	1.249 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)