

# SAC-5P-10,0-BF145/M12FS SH NC - Sensor/actuator cable



1405343

<https://www.phoenixcontact.com/us/products/1405343>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-pos., free cable end to straight M12 socket, A-coded, cable length: 10 m

As shown in the illustration but with different wire colors

## Commercial data

Item number	1405343
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CDA
GTIN	4046356740647
Weight per piece (including packing)	818 g
Weight per piece (excluding packing)	808.8 g
Country of origin	PL

# SAC-5P-10,0-BF145/M12FS SH NC - Sensor/actuator cable



1405343

<https://www.phoenixcontact.com/us/products/1405343>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	5
No. of cable outlets	1
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	48 V AC
	60 V DC

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\geq 100$
-----------------------------	------------

### Signaling

Status display	no
Status display present	no

### Connector

#### Connection 1

Type	free cable end
------	----------------

#### Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A

### Cable/line

Cable length	10 m
--------------	------

#### POC irradiated halogen-free black [BF 145]

Cable weight	86 kg/km
Number of positions	5
Shielded	yes
Cable type	POC irradiated halogen-free black [BF 145]
AWG signal line	20
Conductor cross-section	5x 0.5 mm <sup>2</sup>

# SAC-5P-10,0-BF145/M12FS SH NC - Sensor/actuator cable



1405343

<https://www.phoenixcontact.com/us/products/1405343>

Wire diameter incl. insulation	1.9 mm
External cable diameter	7.30 mm
Outer sheath, material	POC
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	POC
Single wire, color	black 1, black 2, black 3, black 4, black 5
Overall twist	5 wires around filler to the core
Nominal voltage, cable	300 V
Test voltage Core/Core	3500 V
Test voltage Core/Shield	2500.00 V
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	12 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	88 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 10 x D, Traversing path: 5 m, Traversing rate: 4 m/s, Acceleration: 5 m/s <sup>2</sup>
Halogen-free	according to IEC 60754-1 in accordance with DIN EN 50267-2-1
Flame resistance	IEC 60332-1 According to DIN EN 50265-2-1
Concentration of fumes	in accordance with IEC 61034 EN 50268-2
Other resistance	Good resistance to aggressive media
Special properties	Irradiated
Ambient temperature (operation)	-55 °C ... 145 °C (cable, fixed installation) -35 °C ... 120 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket) -25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)


# SAC-5P-10,0-BF145/M12FS SH NC - Sensor/actuator cable

1405343

<https://www.phoenixcontact.com/us/products/1405343>


## Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SAC-5P-10,0-BF145/M12FS SH NC - Sensor/actuator cable



1405343

<https://www.phoenixcontact.com/us/products/1405343>

Circuit diagram



Contact assignment of the M12 socket

# SAC-5P-10,0-BF145/M12FS SH NC - Sensor/actuator cable



1405343

<https://www.phoenixcontact.com/us/products/1405343>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-5P-10,0-BF145/M12FS SH NC - Sensor/actuator cable



1405343

<https://www.phoenixcontact.com/us/products/1405343>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)