

# NBC-M12MRD-M12FRD US/93E/... - Network cable



1405869

<https://www.phoenixcontact.com/us/products/1405869>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT5 (100 Mbps), 4-position, PUR halogen-free, Variable cable type, water blue RAL 5021, shielded, Plug angled M12, coding: D / IP67, on Socket angled M12, coding: D / IP67, cable length: Free input (0.2 m ... 85.0 m)

## Commercial data

|                        |                                |
|------------------------|--------------------------------|
| Item number            | 1405869                        |
| Packing unit           | 1 pc                           |
| Minimum order quantity | 1 pc                           |
| Note                   | Made to order (non-returnable) |
| Sales key              | BF17                           |
| Product key            | AF1IHA                         |
| Customs tariff number  | 85444290                       |
| Country of origin      | US                             |

1405869

<https://www.phoenixcontact.com/us/products/1405869>

## Technical data

### Product properties

|                      |                         |
|----------------------|-------------------------|
| Product type         | Data cable preassembled |
| Application          | Standard, U.S. cables   |
| Number of positions  | 4                       |
| No. of cable outlets | 1                       |
| Shielded             | yes                     |
| Coding               | D                       |

### Interfaces

|                      |                                     |
|----------------------|-------------------------------------|
| Bus system           | Ethernet                            |
| Signal type/category | Ethernet CAT5 (IEC 11801), 100 Mbps |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Electrical properties

|   |  |
|---|--|
| Nominal voltage $U_N$                   | 48 V AC  |
|   | 60 V DC  |
| Nominal current $I_N$                   | 4 A (Plug/socket in accordance with IEC 61076-2-101, cable technical data is to be observed) |
| Transmission medium                     | Copper   |
| Transmission speed                      | 100 Mbps   |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002)  |

### Material specifications

|               |     |
|---------------|-----|
| Seal material | NBR |
|---------------|-----|

### Connector

#### Connection 1

|                      |   |
|----------------------|---|
| Type                 | Plug angled M12 / IP67                                  |
| Coding type          | D (Data)  |
| Handle color         | black   |
| Material             | CuSn (Contact)  |
|                      | Ni/Au (Contact surface)                                 |
|                      | PA (Contact carrier)                                    |
|                      | TPU, hardly inflammable, self-extinguishing (Grip body) |
|                      | Zinc die-cast, nickel-plated (Screw connection)         |
|                      | FKM (Seal)  |
| Degree of protection | IP67  |

#### Connection 2

# NBC-M12MRD-M12FRD US/93E/... - Network cable



1405869


<https://www.phoenixcontact.com/us/products/1405869>

|                      |                          |
|----------------------|--------------------------|
| Type                 | Socket angled M12 / IP67 |
| Coding type          | D (Data)                 |
| Degree of protection | IP67                     |

## Cable/line

|              |                               |
|--------------|-------------------------------|
| Cable length | Free input (0.2 m ... 85.0 m) |
|--------------|-------------------------------|

### Ethernet flexible CAT5, 2-pair [93E]

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |  |
| Cable weight                    | 42 kg/km   |
| UL AWM Style                    | 20963 (80°C/30 V)  |
| Wiring standards/regulations    | Electrical requirements EN 50288-2-2   |
| Number of positions             | 4  |
| Shielded                        | yes  |
| Cable type                      | Ethernet flexible CAT5, 2-pair [93E]   |
| Conductor structure             | 2x2xAWG26/7, SF/UTP  |
| Signal runtime                  | 5.3 ns/m   |
| Conductor structure signal line | 7x 0.16 mm   |
| AWG signal line                 | 26   |
| Conductor cross-section         | 2x 2x 0.14 mm <sup>2</sup>   |
| Wire diameter incl. insulation  | 0.98 mm  |
| External cable diameter         | 6.40 mm ±0.2 mm  |
| Outer sheath, material          | PUR  |
| External sheath, color          | water blue RAL 5021  |
| Conductor material              | Bare Cu litz wires   |
| Material wire insulation        | Foamed PE  |
| Single wire, color              | white/orange-orange, white/green-green   |
| Thickness, outer sheath         | 1.20 mm  |
| Twisted pairs                   | 2 cores to the pair  |
| Overall twist                   | Two pairs with two fillers to the core   |
| Optical shield covering         | 70 %   |
| Insulation resistance           | ≥ 500 MΩ*km  |
| Coupling resistance             | ≤ 100.00 mΩ/m (at 10 MHz)  |
| Loop resistance                 | ≤ 290.00 Ω/km  |
| Wave impedance                  | 100 Ω ±5 Ω (at 100 MHz)  |
| Cable capacity                  | approx. 45 nF/km (at 1 kHz)  |
| Nominal voltage, cable          | ≤ 100 V (Peak value, not for high-power applications)                              |

# NBC-M12MRD-M12FRD US/93E/... - Network cable



1405869

<https://www.phoenixcontact.com/us/products/1405869>

|  |                                      |
|--|--------------------------------------|
| Test voltage Core/Core                                 | 700 V (50 Hz, 1 min.)                |
| Test voltage Core/Shield                               | 700.00 V (50 Hz, 1 min.)             |
| Current carrying capacity of cable                     | 2.00 A (according to DIN VDE 0891-1) |
| Minimum bending radius, fixed installation             | 4 x D                                |
| Minimum bending radius, flexible installation          | 8 x D                                |
| Smallest bending radius, fixed installation            | 26 mm                                |
| Smallest bending radius, movable installation          | 52 mm                                |
| Tensile strength                                       | ≤ 80 N                               |
| Near end crosstalk attenuation (NEXT)                  | 65.3 dB (with 1 MHz)                 |
|  | 56.3 dB (at 4 MHz)                   |
|  | 50.3 dB (at 10 MHz)                  |
|  | 47.2 dB (at 16 MHz)                  |
|  | 45.8 dB (at 20 MHz)                  |
|  | 42.9 dB (at 31.25 MHz)               |
|  | 38.4 dB (at 62.5 MHz)                |
|  | 35.3 dB (at 100 MHz)                 |
| Power-summated near end crosstalk attenuation (PSNEXT) | 62.3 dB (with 1 MHz)                 |
|  | 53.3 dB (at 4 MHz)                   |
|  | 47.3 dB (at 10 MHz)                  |
|  | 44.2 dB (at 16 MHz)                  |
|  | 42.8 dB (at 20 MHz)                  |
|  | 39.9 dB (at 31.25 MHz)               |
|  | 35.4 dB (at 62.5 MHz)                |
|  | 32.3 dB (at 100 MHz)                 |
| Return attenuation (RL)                                | 23 dB (at 4 MHz)                     |
|  | 24.1 dB (at 8 MHz)                   |
|  | 25 dB (at 10 MHz)                    |
|  | 25 dB (at 16 MHz)                    |
|  | 25 dB (at 20 MHz)                    |
|  | 23.6 dB (at 31.25 MHz)               |
|  | 21.5 dB (at 62.5 MHz)                |
|  | 20.1 dB (at 100 MHz)                 |
| Shield attenuation                                     | 3.2 dB (with 1 MHz)                  |
|  | 6 dB (at 4 MHz)                      |
|  | 9.5 dB (at 10 MHz)                   |
|  | 12.1 dB (at 16 MHz)                  |
|  | 13.6 dB (at 20 MHz)                  |
|  | 17.1 dB (at 31.25 MHz)               |
|  | 24.8 dB (at 62.5 MHz)                |
|  | 32 dB (at 100 MHz)                   |
| Halogen-free   | according to IEC 60754-1             |
| Flame resistance                                       | according to IEC 60332-1-2           |
|  | in acc. to UL VW1                    |
|  | in accordance with UN ECE-R 118.03   |

1405869

<https://www.phoenixcontact.com/us/products/1405869>

|                                    |   |
|------------------------------------|---|
| Resistance to oil                  | in accordance with EN 60811-2-1                 |
| Ambient temperature (operation)    | -40 °C ... 80 °C (cable, fixed installation)    |
|                                    | -20 °C ... 80 °C (Cable, flexible installation) |
| Ambient temperature (installation) | -20 °C ... 80 °C                                |

### Environmental and real-life conditions

#### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Degree of protection  | IP65                             |
|   | IP67                             |
|   | IP65/IP67                        |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (M12 connector) |


### Standards and regulations

#### M12

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |


### Drawings

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

Schematic diagram



Pin assignment M12 socket, 4-pos., D-coded, female side

1405869

<https://www.phoenixcontact.com/us/products/1405869>

Circuit diagram



Contact assignment of the M12 connector and the M12 socket

1405869

<https://www.phoenixcontact.com/us/products/1405869>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405869>

|  <b>UL Listed</b><br>Approval ID: FILE E 335024 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 30 V                  | 4 A                   | -                 | -                           |

|  <b>EAC-RoHS</b><br>Approval ID: RU D-DE.HB35.B.00387 |  |
|--|--|
|--|--|

1405869

<https://www.phoenixcontact.com/us/products/1405869>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

1405869

<https://www.phoenixcontact.com/us/products/1405869>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)