

SAC-5P- 2,0-924/FS SCO - Bus system cable



1405986

<https://www.phoenixcontact.com/us/products/1405986>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, CANopen®, DeviceNet™, 5-position, PVC, gray, shielded, free cable end, on Socket straight M12, coding: A, cable length: 2 m, Connector unshielded

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1405986 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF15 |
| Product key | AF1IHE |
| GTIN | 4046356800426 |
| Weight per piece (including packing) | 138 g |
| Weight per piece (excluding packing) | 138 g |
| Customs tariff number | 85444290 |
| Country of origin | US |

SAC-5P- 2,0-924/FS SCO - Bus system cable



1405986

<https://www.phoenixcontact.com/us/products/1405986>

Technical data

Product properties

| | |
|----------------------|-------------------------|
| Product type | Data cable preassembled |
| Application | Standard, U.S. cables |
| Sensor type | CANopen® |
| Number of positions | 5 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | A |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Approvals

National Marine Electronics Association

| | |
|-------------|----------|
| Certificate | approved |
|-------------|----------|

Interfaces

| | |
|----------------------|------------------------|
| Bus system | CANopen®/DeviceNet™ |
| Signal type/category | CANopen® DeviceNet™ |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Electrical properties

| | |
|-----------------------|--------------------|
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U_N | 48 V AC 60 V DC |
| Nominal current I_N | 4 A |
| Transmission medium | Copper |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | HB |
| Seal material | NBR |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | TPU GF |
| Material for screw connection | Zinc die-cast, nickel-plated |

SAC-5P- 2,0-924/FS SCO - Bus system cable



1405986

<https://www.phoenixcontact.com/us/products/1405986>

Connector

Connection 1

| | |
|------|----------------|
| Type | free cable end |
|------|----------------|


Connection 2

| | |
|---------------------|---------------------|
| Type | Socket straight M12 |
| Number of positions | 5 |
| Coding type | A (Standard) |

Cable/line

| | |
|--------------|-----|
| Cable length | 2 m |
|--------------|-----|

CANopen®/DeviceNet™, PVC, gray [924]

| | |
|-------------------------------------|---|
| Dimensional drawing |  |
| Cable weight | 64.51 kg/km |
| UL AWM Style | 2464 (80°C/300 V) |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | CANopen®/DeviceNet™, PVC, gray [924] |
| Conductor structure | 2xAWG22 (Signal) + 2xAWG22 (Power) |
| Signal runtime | 4.46 ns/m |
| Conductor structure signal line | 19x 0.15 mm |
| AWG signal line | 22 |
| Conductor structure, voltage supply | 19x 0.15 mm |
| AWG power supply | 22 |
| Conductor cross-section | 2x 0.34 mm ² (Signal line) 2x 0.34 mm ² (Power supply) |
| Wire diameter incl. insulation | 1.27 mm ±0.05 mm (Signal line) 2.24 mm ±0.13 mm (Power supply) |
| External cable diameter | 6.90 mm ±0.13 mm |
| Outer sheath, material | PVC |
| External sheath, color | gray |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | Foamed PE (Signal line) PVC (Power supply) |
| Single wire, color | red-black, blue-white |

SAC-5P- 2,0-924/FS SCO - Bus system cable



1405986

<https://www.phoenixcontact.com/us/products/1405986>

| | |
|---|---|
| Twisted pairs | 2 cores to the pair |
| Type of pair shielding | Plastic-coated aluminum foil, aluminum side inside |
| Overall twist | 2 pairs around a drain wire in the center to the core |
| Insulation resistance | ≥ 59.38 Ω*m (Signal line) ≥ 57.41 GΩ*km (Power supply) |
| Wave impedance | 120 Ω ±12 Ω |
| Working capacitance | nom. 78.74 pF (per meter) |
| Minimum bending radius, flexible installation | 15 x D |
| Smallest bending radius, movable installation | 104 mm |
| Shield attenuation | 0.95 dB (f = 125 kHz) 1.64 dB (f = 500 kHz) 2.30 dB (f = 1 MHz) |
| Flame resistance | FT4 |
| Resistance to oil | yes |
| Other resistance | UV resistant |
| Special properties | UL standards PLTC and ITC |
| Ambient temperature (operation) | -30 °C ... 75 °C (cable, fixed installation) |

Approvals

National Marine Electronics Association

| | |
|-------------|----------|
| Certificate | approved |
|-------------|----------|

SAC-5P- 2,0-924/FS SCO - Bus system cable

1405986

<https://www.phoenixcontact.com/us/products/1405986>

Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

SAC-5P- 2,0-924/FS SCO - Bus system cable



1405986

<https://www.phoenixcontact.com/us/products/1405986>

Circuit diagram



Contact assignment of the M12 socket

SAC-5P- 2,0-924/FS SCO - Bus system cable



1405986

<https://www.phoenixcontact.com/us/products/1405986>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405986>

|  UL Listed Approval ID: FILE E 221474 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 4 A | - | - |

|  cUL Listed Approval ID: FILE E 221474 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 4 A | - | - |

|  EAC-RoHS Approval ID: RU D-DE.HB35.B.00387 | |
|--|--|
|--|--|

SAC-5P- 2,0-924/FS SCO - Bus system cable



1405986

<https://www.phoenixcontact.com/us/products/1405986>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-5P- 2,0-924/FS SCO - Bus system cable



1405986

<https://www.phoenixcontact.com/us/products/1405986>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Diazene-1,2-dicarboxamide (C,C'-azodi(formamide)) (ADCA)(CAS: 123-77-3) |
| | bis(2-ethylhexyl) tetrabromophthalate covering any of the individual isomers and/or combinations thereof(CAS: 26040-51-7) |
| | 2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9) |
| SCIP | 9f6fab66-6126-48cf-bcec-49833060d8a3 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 1.933 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com