

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable



1406047

<https://www.phoenixcontact.com/us/products/1406047>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, yellow, shielded, Plug straight M8, on free cable end, cable length: 5 m

Commercial data

Item number	1406047
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF13
Product key	AF1IBA
GTIN	4046356799959
Weight per piece (including packing)	171.2 g
Weight per piece (excluding packing)	110.2 g
Customs tariff number	85444290
Country of origin	US

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable



1406047

<https://www.phoenixcontact.com/us/products/1406047>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard, U.S. cables
Number of positions	3
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	PVC

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.2 Nm (M8 connectors)
-------------------	------------------------

Connector

Connection 1

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable



1406047

<https://www.phoenixcontact.com/us/products/1406047>

Type	Plug straight M8
------	------------------

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	5 m
--------------	-----

PVC yellow 105 °C [542]

Dimensional drawing	
Cable weight	33 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	3
Shielded	yes
Cable type	PVC yellow 105 °C [542]
Conductor structure signal line	7x 0.20 mm
AWG signal line	24
Wire diameter incl. insulation	1.12 mm ±0.03 mm
External cable diameter	4.70 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Overall twist	3 wires, twisted
Optical shield covering	85 %
Max. conductor resistance	max. 79.7 Ω/km (20 °C)
Insulation resistance	≥ (550 M Ohms/m @ 500V)
Nominal voltage, cable	300 V
Minimum bending radius, flexible installation	12 x D
Smallest bending radius, movable installation	57 mm
Flame resistance	FT4
Other resistance	UV resistant
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation) -5 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable



1406047

<https://www.phoenixcontact.com/us/products/1406047>

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

Standards and regulations

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable

1406047

<https://www.phoenixcontact.com/us/products/1406047>

Drawings

Dimensional drawing



Plug M8 x 1, straight, shielded

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable

1406047

<https://www.phoenixcontact.com/us/products/1406047>

Circuit diagram



Contact assignment of the M8 plug

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable





1406047


<https://www.phoenixcontact.com/us/products/1406047>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1406047>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

 EAC-RoHS Approval ID: RU D-DE.HB35.B.00387	
--	--

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable



1406047

<https://www.phoenixcontact.com/us/products/1406047>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-M8MS/ 5,0-542 SH BK - Sensor/actuator cable



1406047

<https://www.phoenixcontact.com/us/products/1406047>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c480dba4-f844-4d42-9a05-7f6f8a894ff9

EF3.1 Climate Change

CO2e kg	2.113 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com