

VS-PNRJ45-PNRJ45-93B-3,5 - Patch cable

1406402

<https://www.phoenixcontact.com/us/products/1406402>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 3.5 m, number of positions: 4, 100 Mbps, PROFINET, 1x4xAWG22/7, SF/TQ, green RAL 6018

PROFINET patch cable

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1406402 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB11 |
| Product key | ABNABA |
| GTIN | 4046356763448 |
| Weight per piece (including packing) | 256.2 g |
| Weight per piece (excluding packing) | 249.685 g |
| Customs tariff number | 85444210 |
| Country of origin | PL |

VS-PNRJ45-PNRJ45-93B-3,5 - Patch cable



1406402

<https://www.phoenixcontact.com/us/products/1406402>

Technical data

Product properties

| | |
|---------------------|--------------------------|
| Product type | Data cable preassembled |
| Product family | RJ45 INDUSTRIAL PN4 CAT5 |
| Application | Standard |
| Sensor type | PROFINET |
| Number of positions | 4 |
| Shielded | yes |

Insulation characteristics

| | |
|----------------------|---|
| Overvoltage category | I |
|----------------------|---|

Signaling

| | |
|----------------|----|
| Status display | no |
|----------------|----|

Electrical properties

| | |
|---|-----------|
| Rated voltage (III/3) | 72 V (DC) |
| Transmission medium | Copper |
| Transmission speed | 100 Mbps |
| Transmission characteristics (category) | CAT5 |
| Transmission speed | 100 Mbps |

Mechanical properties

Mechanical data

| | |
|-------------------------------------|---------|
| Insertion force per signal contact | 50.00 N |
| Extraction force per signal contact | 30 N |

Connector

Connection 1

| | |
|----------------------|--------------------|
| Type | Plug straight RJ45 |
| Shielded | yes |
| Degree of protection | IP20 |

Connection 2

| | |
|-----------------------------|--------------------|
| Type | Plug straight RJ45 |
| Shielded | yes |
| Insertion/withdrawal cycles | ≥ 750 |
| Degree of protection | IP20 |

Cable/line


| | |
|--------------|--------|
| Cable length | 3.50 m |
|--------------|--------|

PROFINET PVC stranded CAT5 [93B]

VS-PNRJ45-PNRJ45-93B-3,5 - Patch cable

1406402

<https://www.phoenixcontact.com/us/products/1406402>

| | |
|---|--|
| Dimensional drawing |  |
| Note | Minimum bending radius 4 x D |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | PROFINET PVC stranded CAT5 [93B] |
| Conductor structure | 1x4xAWG22/7, SF/TQ |
| Conductor structure signal line | 7x 0.25 mm |
| AWG signal line | 22 |
| Conductor cross-section | 4x 0.34 mm ² |
| Wire diameter incl. insulation | approx. 1.5 mm |
| External cable diameter | 6.50 mm |
| Outer sheath, material | PVC |
| External sheath, color | green RAL 6018 |
| Conductor material | Tin-plated Cu litz wires |
| Single wire, color | white, yellow, blue, orange |
| Wave impedance | 100 Ω ±15 Ω (at 1 ... 100 MHz) |
| Smallest bending radius, fixed installation | 30 mm |
| Smallest bending radius, movable installation | 60 mm |
| Ambient temperature (operation) | -25 °C ... 80 °C -25 °C ... 80 °C |

VS-PNRJ45-PNRJ45-93B-3,5 - Patch cable

1406402

<https://www.phoenixcontact.com/us/products/1406402>

Drawings

Schematic diagram



Circuit diagram



VS-PNRJ45-PNRJ45-93B-3,5 - Patch cable



1406402

<https://www.phoenixcontact.com/us/products/1406402>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

VS-PNRJ45-PNRJ45-93B-3,5 - Patch cable



1406402

<https://www.phoenixcontact.com/us/products/1406402>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com