

SACB-SH-8 PARA VA MOUNT P-PROT - Distributor box



1407295

<https://www.phoenixcontact.com/us/products/1407295>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, connection method: M12 socket Stainless steel, number of slots: 8, number of positions: 5, coding: A, slot assignment: parallel, status display: no, Universal, shielding: yes

The figure shows the version without locking screw

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1407295 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF44 |
| Product key | AF3EAA |
| GTIN | 4046356772273 |
| Weight per piece (including packing) | 537.3 g |
| Weight per piece (excluding packing) | 537.3 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

SACB-SH-8 PARA VA MOUNT P-PROT - Distributor box



1407295

<https://www.phoenixcontact.com/us/products/1407295>

Technical data

Notes

| | |
|---------------------|---|
| Assembly note | NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
| Note on application | Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories". |

Product properties

| | |
|---------------------|-----------------|
| Product type | Distributor box |
| Number of positions | 5 |
| Number of slots | 8 |
| Coding | A |

Electrical properties

| | |
|---|---------|
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |
| Rated current, total | 4 A |
| Max. current carrying capacity per path | 2 A |
| Current carrying capacity per slot | 4 A |

Connection data

Conductor connection

| | |
|--|------------|
| Sensor/actuator connection system | M12 socket |
| Tightening torque slot sensor/actuator cable | 0.4 Nm |

Signaling

| | |
|------------------------|----|
| Status display present | no |
|------------------------|----|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 60 mm |
| Height | 35 mm |
| Length | 170 mm |

Material specifications

| | |
|--------------------------|------------------------|
| Material Threaded sleeve | Stainless steel 1.4404 |
|--------------------------|------------------------|

SACB-SH-8 PARA VA MOUNT P-PROT - Distributor box



1407295

<https://www.phoenixcontact.com/us/products/1407295>

| | |
|--|------------------------|
| Material Housing | Stainless steel 1.4404 |
| Material Molding compound | PUR |
| Flammability rating according to UL 94 | V0 |
| Seal material O-ring | FKM |
| Contact material | CuSn6 |
| Contact surface material | gold-plated |
| Contact carrier material | PBT |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP65 |
| | IP67 |
| Ambient temperature (operation) | -30 °C ... 80 °C |

Standards and regulations

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |

SACB-SH-8 PARA VA MOUNT P-PROT - Distributor box




1407295

<https://www.phoenixcontact.com/us/products/1407295>

Drawings

Dimensional drawing



SACB-SH-8 PARA VA MOUNT P-PROT - Distributor box



1407295


<https://www.phoenixcontact.com/us/products/1407295>

Schematic diagram



M12 slot, socket, 5-pos.

Circuit diagram



SACB-SH-8 PARA VA MOUNT P-PROT - Distributor box



1407295

<https://www.phoenixcontact.com/us/products/1407295>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440111 |
| ECLASS-15.0 | 27440111 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003558 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

SACB-SH-8 PARA VA MOUNT P-PROT - Distributor box



1407295

<https://www.phoenixcontact.com/us/products/1407295>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com