

# CUC-IND-C1ZNI-B/R4QV6 - RJ45 connector



1406338

<https://www.phoenixcontact.com/us/products/1406338>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 6, 100 Mbps, CAT5 (IEC 11801:2002), material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: angled, High degree of resistance to vibration; 360° shielding; one-piece design; special tool-free assembly, VARAN

## Your advantages

- Easy and time-saving assembly with IDC fast connection technology
- Can be used internationally due to EAC, UL 1863, and CAN/CSA C22.2
- Ideal companion for servicing or repairs in the field: no special tools required for mounting

## Commercial data

Item number	1406338
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNAAA
GTIN	4046356760744
Weight per piece (including packing)	30 g
Weight per piece (excluding packing)	17.213 g
Customs tariff number	85366990
Country of origin	PL

1406338

<https://www.phoenixcontact.com/us/products/1406338>

## Technical data

### Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	VARAN
Number of positions	6
Connection profile	RJ45
No. of cable outlets	1
Cable outlet	angled
Positions/contacts	8P6C

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Contact resistance	< 20 mΩ (Contact) < 100 mΩ (shield)
Frequency range	to 100 MHz
Insulation resistance	> 500 MΩ
Nominal voltage $U_N$	48 V
Nominal current $I_N$	1.75 A
Contact resistance per contact pair	< 20 Ω
Contact resistance	> 10 mΩ (Wire – IDC) 0.005 Ω (Litz wires – IDC)
Transmission medium	Copper
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

### Connection data

#### Connection technology

Connection method	Insulation displacement connection
Connection cross section AWG	4x 26 ... 24 (Data (solid and stranded)) 2x 26 ... 24 (Power (solid and stranded))
Conductor cross-section	4x 0.25 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> (Data (solid and stranded)) 2x 0.23 mm <sup>2</sup> ... 0.32 mm <sup>2</sup> (Power (solid and stranded))

### Dimensions

Width	13.65 mm
-------	----------

# CUC-IND-C1ZNI-B/R4QV6 - RJ45 connector



1406338

<https://www.phoenixcontact.com/us/products/1406338>

Height	40 mm
Length	37.95 mm

## Material specifications

Material	Plastic
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	Ni
Cable seal material	NBR
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
Locking latch material	Stainless steel
Material for screw connection	PA

## Cable/line

External cable diameter	5 mm ... 9 mm
External cable diameter	5 mm ... 9 mm
Wire diameter including insulation	≤ 1.6 mm
Cable cross section	0.25 mm <sup>2</sup>
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500.00 V

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 750
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

## Environmental and real-life conditions

### Test specification

Type of test	Vibration test
Specification	IEC 60068-2-6
Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s <sup>2</sup>
Test duration	20.00 s

## Mounting

Mounting type	For field assembly
---------------	--------------------

# CUC-IND-C1ZNI-B/R4QV6 - RJ45 connector



1406338

<https://www.phoenixcontact.com/us/products/1406338>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1406338>

 <b>cULus Recognized</b> Approval ID: E335024-20170228				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	56.5 V	1.75 A	-	-

# CUC-IND-C1ZNI-B/R4QV6 - RJ45 connector



1406338

<https://www.phoenixcontact.com/us/products/1406338>

## Classifications

### ECLASS

ECLASS-13.0	27440114
ECLASS-15.0	27440114

### ETIM

ETIM 10.0	EC002636
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-IND-C1ZNI-B/R4QV6 - RJ45 connector



1406338

<https://www.phoenixcontact.com/us/products/1406338>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)