

# VS-PNRJ45-PNRJ45-93B-20,0 - Patch cable



1406408

<https://www.phoenixcontact.com/us/products/1406408>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 20 m, number of positions: 4, 100 Mbps, PROFINET, 1x4xAWG22/7, SF/TQ, green RAL 6018

PROFINET patch cable

## Commercial data

Item number	1406408
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB11
Product key	ABNABA
GTIN	4046356764100
Weight per piece (including packing)	1,266.056 g
Weight per piece (excluding packing)	1,266.056 g
Customs tariff number	85444210
Country of origin	PL

# VS-PNRJ45-PNRJ45-93B-20,0 - Patch cable



1406408

<https://www.phoenixcontact.com/us/products/1406408>

## Technical data

### Product properties

Product type	Data cable preassembled
Product family	RJ45 INDUSTRIAL PN4 CAT5
Application	Standard
Sensor type	PROFINET
Number of positions	4
Shielded	yes

### Insulation characteristics

Overvoltage category	I
----------------------	---

### Signaling

Status display	no
----------------	----

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Transmission medium	Copper
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

### Mechanical properties

#### Mechanical data

Insertion force per signal contact	50.00 N
Extraction force per signal contact	30 N

### Connector

#### Connection 1

Type	Plug straight RJ45
Shielded	yes
Degree of protection	IP20

#### Connection 2

Type	Plug straight RJ45
Shielded	yes
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

### Cable/line


Cable length	20.00 m
--------------	---------

PROFINET PVC stranded CAT5 [93B]

# VS-PNRJ45-PNRJ45-93B-20,0 - Patch cable

1406408

<https://www.phoenixcontact.com/us/products/1406408>

Dimensional drawing	
Note	Minimum bending radius 4 x D
Number of positions	4
Shielded	yes
Cable type	PROFINET PVC stranded CAT5 [93B]
Conductor structure	1x4xAWG22/7, SF/TQ
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Conductor cross-section	4x 0.34 mm <sup>2</sup>
Wire diameter incl. insulation	approx. 1.5 mm
External cable diameter	6.50 mm
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Conductor material	Tin-plated Cu litz wires
Single wire, color	white, yellow, blue, orange
Wave impedance	100 Ω ±15 Ω (at 1 ... 100 MHz)
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm
Ambient temperature (operation)	-25 °C ... 80 °C -25 °C ... 80 °C

# VS-PNRJ45-PNRJ45-93B-20,0 - Patch cable



1406408

<https://www.phoenixcontact.com/us/products/1406408>

## Drawings

Schematic diagram



Circuit diagram



# VS-PNRJ45-PNRJ45-93B-20,0 - Patch cable



1406408

<https://www.phoenixcontact.com/us/products/1406408>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1406408>



**EAC**

Approval ID: 19060508

# VS-PNRJ45-PNRJ45-93B-20,0 - Patch cable



1406408

<https://www.phoenixcontact.com/us/products/1406408>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-PNRJ45-PNRJ45-93B-20,0 - Patch cable



1406408

<https://www.phoenixcontact.com/us/products/1406408>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)