

SAC-5P-MSB/ 0,5-PVC SCO - Sensor/actuator cable



1406442

<https://www.phoenixcontact.com/us/products/1406442>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, PVC, black RAL 9005, Plug straight M12 SPEEDCON, coding: A, on free cable end, cable length: 0.5 m

Commercial data

Item number	1406442
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CDA
GTIN	4046356766814
Weight per piece (including packing)	38.5 g
Weight per piece (excluding packing)	36 g
Country of origin	PL

SAC-5P-MSB/ 0,5-PVC SCO - Sensor/actuator cable



1406442

<https://www.phoenixcontact.com/us/products/1406442>

Technical data

Product properties

Product type	Sensor/actuator cable
No. of cable outlets	1
Coding	A

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Locking type	SPEEDCON
Coding type	A

Connection 2


Type	free cable end
------	----------------

Cable/line

Cable length	0.5 m
--------------	-------

PVC black [PVC]

Dimensional drawing



Cable weight	51 kg/km
UL AWM Style	2464 / 1729 (80°C/300 V)
Number of positions	5
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor cross-section	5x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.26 mm \pm 0.05 mm
External cable diameter	5.00 mm \pm 0.15 mm
Outer sheath, material	PVC

SAC-5P-MSB/ 0,5-PVC SCO - Sensor/actuator cable



1406442

<https://www.phoenixcontact.com/us/products/1406442>

External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black, green-yellow
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	5 wires around filler to the core
Max. conductor resistance	max. 57 Ω/km (at 20 °C)
Insulation resistance	≥ 200 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	25 mm
Smallest bending radius, movable installation	50 mm
Flame resistance	UL VW-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -10 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-5P-MSB/ 0,5-PVC SCO - Sensor/actuator cable



1406442

<https://www.phoenixcontact.com/us/products/1406442>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

1406442

<https://www.phoenixcontact.com/us/products/1406442>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com