

# SAC-3P- 5,0-PUR/FR-2L SCO - Sensor/actuator cable



1407776

<https://www.phoenixcontact.com/us/products/1407776>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket angled M12 SPEEDCON, coding: A, with 2 LEDs, cable length: 5 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with SPEEDCON fast locking system
- Our standard: robust halogen-free PUR cable
- Convenient: increased machine availability thanks to quick and easy diagnostics

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1407776                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF03                           |
| Product key                          | AF1CBA                         |
| GTIN                                 | 4046356790291                  |
| Weight per piece (including packing) | 138.7 g                        |
| Weight per piece (excluding packing) | 133.1 g                        |
| Customs tariff number                | 85444290                       |
| Country of origin                    | PL                             |

# SAC-3P- 5,0-PUR/FR-2L SCO - Sensor/actuator cable



1407776

<https://www.phoenixcontact.com/us/products/1407776>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 3                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | HB  |
| Seal material                          | NBR   |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn  |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 24 V AC                    |
|                       | 24 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |        |
|------------------------|--------|
| Status display         | 2 LEDs |
| Status display present | yes    |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

### Connector

#### Connection 1

# SAC-3P- 5,0-PUR/FR-2L SCO - Sensor/actuator cable



1407776

<https://www.phoenixcontact.com/us/products/1407776>

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Connection 2

|                     |                            |
|---------------------|----------------------------|
| Type                | Socket angled M12 SPEEDCON |
| Number of positions | 3                          |
| Locking type        | SPEEDCON                   |
| Coding type         | A                          |

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 5 m |
|--------------|-----|

## PUR halogen-free black [PUR]

|   |   |
|---|---|
| Dimensional drawing                           |  |
| Cable weight                                  | 23 kg/km  |
| UL AWM Style                                  | 20549   |
| Number of positions                           | 3   |
| Shielded                                      | no  |
| Cable type                                    | PUR halogen-free black [PUR]  |
| Conductor structure signal line               | 42x 0.10 mm   |
| AWG signal line                               | 22  |
| Conductor cross-section                       | 3x 0.34 mm <sup>2</sup> (Signal line)   |
| Wire diameter incl. insulation                | 1.27 mm ±0.02 mm (Signal line)  |
| External cable diameter                       | 3.85 mm ±0.15 mm  |
| Outer sheath, material                        | PUR   |
| External sheath, color                        | black-gray RAL 7021   |
| Conductor material                            | Bare Cu litz wires  |
| Material wire insulation                      | PP  |
| Single wire, color                            | brown, blue, black  |
| Thickness, insulation                         | ≥ 0.21 mm (Core insulation)<br>approx. 0.50 mm (Outer cable sheath)                 |
| Overall twist                                 | 3 wires, twisted  |
| Max. conductor resistance                     | max. 58 Ω/km (at 20 °C)   |
| Insulation resistance                         | ≥ 100 GΩ*km (at 20 °C)  |
| Nominal voltage, cable                        | ≤ 300 V   |
| Test voltage                                  | ≥ 3000 V  |
| Smallest bending radius, fixed installation   | 19 mm   |
| Smallest bending radius, movable installation | 38 mm   |
| Dynamic load capacity (bending)               | Max. bending cycles: 10000000, Bending radius: 38 mm,                               |

# SAC-3P- 5,0-PUR/FR-2L SCO - Sensor/actuator cable



1407776

<https://www.phoenixcontact.com/us/products/1407776>

|                                 |  |
|---------------------------------|--|
|                                 | Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup> |
| Dynamic load capacity (torsion) | Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.                         |
| Halogen-free                    | in accordance with DIN VDE 0472 part 815   |
| Flame resistance                | in accordance with UL 758/1581 FT2   |
|                                 | DIN EN 60332-2-2 (20 s)  |
| Resistance to oil               | in accordance with DIN EN 60811-2-1  |
| Other resistance                | Highly resistant to acids, alkaline solutions and solvents   |
|                                 | hydrolysis and microbe resistant   |
|                                 | partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)   |
| Special properties              | Flexible cable conduit capable   |
|                                 | Silicone-free  |
|                                 | Free of substances which would hinder coating with paint or varnish                                      |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)   |
|                                 | -25 °C ... 80 °C (Cable, flexible installation)  |

## Environmental and real-life conditions

### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Degree of protection  | IP65                             |
|   | IP67                             |
|   | IP68                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

# SAC-3P- 5,0-PUR/FR-2L SCO - Sensor/actuator cable

1407776

<https://www.phoenixcontact.com/us/products/1407776>

## Drawings

Dimensional drawing



Socket M12 x 1, angled, with LED

Schematic diagram



Pin assignment M12 socket, 3-pos., A-coded, view female side

# SAC-3P- 5,0-PUR/FR-2L SCO - Sensor/actuator cable



1407776

<https://www.phoenixcontact.com/us/products/1407776>

Circuit diagram



Contact assignment of the M12 socket

# SAC-3P- 5,0-PUR/FR-2L SCO - Sensor/actuator cable



1407776

<https://www.phoenixcontact.com/us/products/1407776>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

# SAC-3P- 5,0-PUR/FR-2L SCO - Sensor/actuator cable



1407776

<https://www.phoenixcontact.com/us/products/1407776>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)