

# NBC-M12MRD/10,0-93E/R4AC S - Network cable



1407832

<https://www.phoenixcontact.com/us/products/1407832>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet, 4-position, shielded, Plug angled M12, coding: D, on Plug straight RJ45, cable length: 10 m

## Commercial data

Item number	1407832
Packing unit	4 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Product key	AF1CJI
GTIN	4046356773706
Weight per piece (including packing)	450.5 g
Weight per piece (excluding packing)	450.5 g
Country of origin	PL

1407832

<https://www.phoenixcontact.com/us/products/1407832>

## Technical data

### Product properties

Product type	Data cable preassembled
Number of positions	4

### Interfaces

Bus system	Ethernet
Signal type/category	Ethernet

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC

### Material specifications

Outer sheath, material	PUR
------------------------	-----

### Connector

#### Connection 1

Type	Plug angled M12
Coding type	D (Data)

#### Connection 2

Type	Plug straight RJ45
------	--------------------

### Cable/line

Cable length	10 m
Signal type/category	Ethernet
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021

# NBC-M12MRD/10,0-93E/R4AC S - Network cable



1407832

<https://www.phoenixcontact.com/us/products/1407832>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# NBC-M12MRD/10,0-93E/R4AC S - Network cable



1407832

<https://www.phoenixcontact.com/us/products/1407832>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)