

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable



1407331

<https://www.phoenixcontact.com/us/products/1407331>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PE-X halogen-free, black, shielded, free cable end, on Socket straight M12 SPEEDCON, coding: A, cable length: 2 m, For railway applications

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Securely locked by special vibration brake
- Resistant to temperature influences – tested for an extended temperature range and for resistance to temperature shocks
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1407331 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF03 |
| Product key | AF1CDA |
| GTIN | 4046356774475 |
| Weight per piece (including packing) | 159.1 g |
| Weight per piece (excluding packing) | 158 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable



1407331

<https://www.phoenixcontact.com/us/products/1407331>

Technical data

Product properties

| | |
|----------------------|-----------------------|
| Product type | Sensor/actuator cable |
| Application | Railway applications |
| Number of positions | 5 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | A |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Material specifications

| | |
|--|------------------------------|
| Flammability rating according to UL 94 | V0 |
| Seal material | NBR |
| Material of grip body | PA 6.6 |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | PA 6.6 |
| Material for screw connection | Zinc die-cast, nickel-plated |
| Standards/regulations | PA 6.6 |

Electrical properties

| | |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |
| Nominal current I_N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|------------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|------------|

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Connection data

Conductor connection

| | |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

Connector

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable

1407331

<https://www.phoenixcontact.com/us/products/1407331>

Connection 1

| | |
|------|----------------|
| Type | free cable end |
|------|----------------|

Connection 2

| | |
|---------------------|------------------------------|
| Type | Socket straight M12 SPEEDCON |
| Number of positions | 5 |
| Locking type | SPEEDCON |
| Coding type | A |

Cable/line

| | |
|--------------|-----|
| Cable length | 2 m |
|--------------|-----|

Shielded black RADOX® [28R]

| | |
|---------------------------------|---|
| Dimensional drawing |  |
| Cable weight | 70 kg/km |
| Number of positions | 5 |
| Shielded | yes |
| Cable type | Shielded black RADOX® [28R] |
| Conductor structure signal line | 19x 0.18 mm |
| AWG signal line | 20 |
| Conductor cross-section | 5x 0.5 mm ² |
| Wire diameter incl. insulation | 1.43 mm |
| External cable diameter | 6.20 mm ±0.3 mm |
| Outer sheath, material | PE-X |
| External sheath, color | black |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | PE-X |
| Single wire, color | white 1, white 2, white 3, white 4, white 5 |
| Overall twist | 5 cores, twisted |
| Max. conductor resistance | ≤ 40.1 Ω/km |
| Nominal voltage, cable | 600 V AC (Core-ground, U ₀) 1000 V AC (Core-ground, U) ≤ 720 V AC (core-ground) ≤ 1200 V AC (Core-ground, U _m) ≤ 900 V DC (Core-ground, V ₀) ≤ 1500 V DC (Line-line) |
| Test voltage | 3500 V AC (50 Hz, 5 min.) |

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable



1407331

<https://www.phoenixcontact.com/us/products/1407331>

| | |
|---|--|
| | 8400 V DC (50 Hz, 5 min.) |
| Minimum bending radius, fixed installation | 3 x D |
| Minimum bending radius, flexible installation | 4 x D |
| Smallest bending radius, fixed installation | 19 mm |
| Smallest bending radius, movable installation | 25 mm |
| Halogen-free | in accordance with EN 50267-2-1 |
| Flame resistance | IEC 60332-1-2 |
| | EN 50266 |
| | EN 60332-3-25 |
| | NF C32-070, 2.1 |
| | NF C32-070, 2.2 |
| | UL 1685, 12 (FT4) |
| | in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01) |
| Fume corrosiveness | EN 50267-2-2 |
| Fume toxicity | BS 6853 B.1 |
| | EN 50305, 9.2 |
| Concentration of fumes | BS 6853 D.8.7 |
| | EN 61034-2 |
| | UL 1685, 12 (FT4) |
| Resistance to oil | according to IRM 902, 72 h at 100 °C |
| Fire protection in rail vehicles | BS 6853 (Category Ia, Ib, II) |
| | GM/RT 2130 (Category Ia, Ib, II) |
| | EN 45545 (Risk level HL1 - HL3) |
| | DIN 5510 (Fire protection level 1, 2, 3, 4) |
| | NF F16-101 (Category A1, A2, B) |
| | NF F16-101 (Class C/F0) |
| | NFPA 130 |
| UNI CEI 11170 (Risk level LR1 - LR4) | |
| Other resistance | Resistance to fuels (according to IRM 903, 168 h at 70 °C) |
| Ambient temperature (operation) | -50 °C ... 120 °C (cable, fixed installation) |
| | -25 °C ... 90 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|----------------------------------|
| Degree of protection | IP65 |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C (Plug / socket) |

Standards and regulations

M12

| | |
|--------------------------|------------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |
| Standard designation | Shock, vibration |

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable



1407331

<https://www.phoenixcontact.com/us/products/1407331>

Standards/specifications

EN 50155

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable

1407331

<https://www.phoenixcontact.com/us/products/1407331>


Drawings

Dimensional drawing



Socket M12-SPEEDCON, straight, shielded

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable



1407331

<https://www.phoenixcontact.com/us/products/1407331>

Circuit diagram



Contact assignment of the M12 socket

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable



1407331

<https://www.phoenixcontact.com/us/products/1407331>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1407331>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable



1407331

<https://www.phoenixcontact.com/us/products/1407331>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-5P- 2,0-28R/FS SCO RAIL - Sensor/actuator cable



1407331

<https://www.phoenixcontact.com/us/products/1407331>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) |
| SCIP | d95d18a1-874a-4136-b188-76a3f61f34a9 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 1.206 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com