

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket



1408170

<https://www.phoenixcontact.com/us/products/1408170>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect basic, GB/T, Infrastructure charging socket, 32 A , 440 V AC, Gen 1, Single-core wires connected at one end, length: 0.7 m, square, Front and rear mounting, housing: black, for charging electric vehicles with alternating current (AC), GB/T 20234.2-2015, NOTE This product version does not include a locking actuator.

Product description

Infrastructure charging socket for charging electric vehicles (EV) with alternating current (AC), compatible with GB/T Infrastructure Plugs, for installation at charging stations for E-Mobility (EVSE)

Your advantages

- Complete product range
- Uniform, space-saving installation space
- Available with your logo on request - for consistent branding of your charging station
- Integrated interlock during charging
- Manual emergency release of the locking actuator
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1408170 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | EM01 |
| Product key | XWBFBA |
| GTIN | 4046356856041 |
| Weight per piece (including packing) | 699 g |
| Weight per piece (excluding packing) | 699 g |
| Customs tariff number | 85444290 |
| Country of origin | CN |

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket



1408170

<https://www.phoenixcontact.com/us/products/1408170>

Technical data

Product properties

| | |
|---|--------------------------------|
| Product type | Infrastructure charging socket |
| Product family | CHARX connect basic |
| Type | Gen 1 |
| Charging standard | GB/T |
| Charging mode | Mode 3, Case B |
| Design (Infrastructure charging socket) | square |
| Customer variations | On request |

Electrical properties

| | |
|-------------------------------|--|
| Note on the connection method | Crimp connection, cannot be disconnected |
|-------------------------------|--|

Charging power and current (AC charging, 3-phase)

| | |
|--------------------------|-----------------------|
| Type of charging current | AC 3-phase |
| Charging current | 32 A AC (3-phase) |
| Charging power | 26.6 kW (3-phase) |
| Charging power rating | 22 kW (32 A, 3-phase) |
| Operating voltage | typ. 380 V AC |

Pin assignment (Power contacts)

| | |
|---------------|-----------------------|
| Number | 5 (L1, L2, L3, N, PE) |
| Rated voltage | 440 V AC |
| Rated current | 32 A |

Pin assignment (Signal contacts)

| | |
|-----------------------------|------------------------|
| Type of signal transmission | Pulse width modulation |
| Number | 2 (CP, CC) |
| Rated voltage | 30 V AC |
| Rated current | 2 A |

Locking actuator

| | |
|------------------|--------------------------|
| Locking actuator | without locking actuator |
|------------------|--------------------------|

Dimensions

Infrastructure charging socket

| | |
|---------------------|--|
| Dimensional drawing | |
|---------------------|--|


EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket

1408170

<https://www.phoenixcontact.com/us/products/1408170>

| | |
|--------|---------------------|
| | Dimensional drawing |
| Width | 75 mm |
| Height | 96 mm |
| Depth | 76.2 mm |

Bore dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| | Hole image |
| Width | 60 mm |
| Height | 60 mm |

Material specifications

| | |
|--|--------------|
| Color (Housing) | black (9005) |
| Material (Housing) | Plastic |
| Material (Contact surface) | Silver |
| Flammability rating according to UL 94 | V0 () |

Cable/line

| | |
|----------------------------|---|
| Cable length | 0.7 m |
| Cable type | Single-core wires connected at one end |
| Cable structure | 5x 6.0 mm ² + 2x 0.5 mm ² |
| Single wire, cross section | 6.00 mm ² |

Single-core wires for AC

| | |
|--------------|-------|
| Cable length | 0.7 m |
|--------------|-------|

Mechanical properties

Mechanical data

| | |
|-----------------------------|---------|
| Insertion/withdrawal cycles | > 10000 |
| Insertion force | < 100 N |
| Withdrawal force | < 100 N |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Degree of protection (Infrastructure charging socket) | IP55 (plugged in) |
| Ambient temperature (operation) | -30 °C ... 50 °C |

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket



1408170

<https://www.phoenixcontact.com/us/products/1408170>

| | |
|---|--------------------------|
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | 5000 m (above sea level) |

Standards and regulations

Standards

| | |
|-----------------------|-------------------|
| Standards/regulations | GB/T 20234.2-2015 |
|-----------------------|-------------------|

Mounting

| | |
|--|---|
| Mounting type Infrastructure charging socket | Front and rear mounting (0 to 90 degree frontal inclination possible) |
| Mounting type Protective cover | rear (available separately) |
| Mounting hole diameter | 7.00 mm (ø) |

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket

1408170

<https://www.phoenixcontact.com/us/products/1408170>

Drawings

Dimensional drawing




Hole image

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket

1408170


<https://www.phoenixcontact.com/us/products/1408170>

Dimensional drawing



Dimensional drawing

Connection diagram




Pin assignment of infrastructure charging socket

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket

1408170

<https://www.phoenixcontact.com/us/products/1408170>

Schematic diagram




Rear mounting

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket

1408170

<https://www.phoenixcontact.com/us/products/1408170>

Schematic diagram



Front mounting with rear protective cover screw connection


The screw connection for a protective cover from the accessories range (EV-GBSC...) only supports rear mounting.

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket

1408170


<https://www.phoenixcontact.com/us/products/1408170>

Schematic diagram



Operating instructions

Schematic diagram




Installation positions

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket

1408170

<https://www.phoenixcontact.com/us/products/1408170>

Block diagram



Block diagram of the locking actuator

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket



1408170

<https://www.phoenixcontact.com/us/products/1408170>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27144706 |
| ECLASS-15.0 | 27144706 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002898 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121800 |
|-------------|----------|

EV-GBM3S-3AC32A-0,7M6,0E00 - Infrastructure charging socket



1408170

<https://www.phoenixcontact.com/us/products/1408170>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com