

HC-COM-17-ESTC - Contact insert



1408465

<https://www.phoenixcontact.com/us/products/1408465>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 17+PE, size: COM, power contacts: 0, control contacts: 17, number of connections per position: 1, Pin, Crimp connection, 200 V, 10 A, 0.14 mm² ... 2.5 mm², application: Power, Only suitable for plastic housings

Product description

Contact insert, incl. 4 mounting screws

Your advantages

- Shock and vibration-resistant in accordance with DIN EN 61373

Commercial data

Item number	1408465
Packing unit	2 pc
Minimum order quantity	2 pc
Sales key	BF61
Product key	AF7ABH
GTIN	4046356618175
Weight per piece (including packing)	15.9 g
Weight per piece (excluding packing)	15.9 g
Customs tariff number	85389099
Country of origin	CN

HC-COM-17-ESTC - Contact insert



1408465

<https://www.phoenixcontact.com/us/products/1408465>

Technical data

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---


Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-COM
Application	Power
Type	COM
Number of positions	17
Connection profile	17+PE
Contact numbering	1 - 17
Number of connections per position	1
No. of power contacts	0
No. of control contacts	17
Contact material type	turned rolled

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Dimensional drawing	
Width	25.6 mm
Height	38.7 mm
Length	45 mm

Mechanical characteristics

Contact diameter	1.6 mm
------------------	--------

Connection data

Connection technology

Connection technology	Crimp connection
Number of connections per position	1
Connection in acc. with standard	IEC / EN

Conductor connection

HC-COM-17-ESTC - Contact insert



1408465

<https://www.phoenixcontact.com/us/products/1408465>

Conductor cross-section	0.14 mm ² ... 2.5 mm ²
Connection cross section AWG	26 ... 14
Stripping length of the individual wire	8 mm
	6 mm (at 2.5 mm ²)

Electrical properties

Rated voltage (III/2) contacts	250 V
Rated voltage (III/3)	200 V
Rated voltage for power contacts	200
Rated surge voltage	4 kV
Rated current	10 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Seal material Profile gasket	NBR
Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C (including heating up of contacts)
---------------------------------	--

HC-COM-17-ESTC - Contact insert




1408465

<https://www.phoenixcontact.com/us/products/1408465>

Drawings

Dimensional drawing



HC-COM-17-ESTC dimensional drawing


HC-COM-17-ESTC - Contact insert

1408465

<https://www.phoenixcontact.com/us/products/1408465>



Schematic diagram




Connector pin assignment, connection side

HC-COM-17-ESTC - Contact insert



1408465

<https://www.phoenixcontact.com/us/products/1408465>



Derating diagram

HC-COM-17-ESTC - Contact insert





1408465


<https://www.phoenixcontact.com/us/products/1408465>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1408465>

 CSA Approval ID: 260458				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	19 A	20 - 12	-

 cUL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	10.5 A	22 - 14	-

 UL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	19.5 A	22 - 14	-

 EAC Approval ID: RU C-DE.AI30.B.01102				
---	--	--	--	--

HC-COM-17-ESTC - Contact insert



1408465

<https://www.phoenixcontact.com/us/products/1408465>

Classifications

ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

ETIM

ETIM 10.0	EC000438
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

1408465

<https://www.phoenixcontact.com/us/products/1408465>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Perfluorobutane sulfonic acid (PFBS) and its salts(CAS: n/a)
	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	98763ff0-3ff2-40be-99b0-e1cb495ebf35

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com