

SAC-ASI-J-Y-B-PUR-2,0-OE - Distributor



1407581

<https://www.phoenixcontact.com/us/products/1407581>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-Interface distributor with a high degree of protection, for a branch from two flat-ribbon conductors to a 2.0 m PUR round cable with free cable end

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1407581 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF10 |
| Product key | AF1GFA |
| GTIN | 4046356780018 |
| Weight per piece (including packing) | 98 g |
| Weight per piece (excluding packing) | 96.5 g |
| Customs tariff number | 85444290 |
| Country of origin | VN |

1407581

<https://www.phoenixcontact.com/us/products/1407581>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Network distributor box |
| Number of positions | 4 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|-----------------------|----------------|
| Nominal voltage U_N | ≤ 32 V DC |
| Nominal current I_N | 4 A |
| Transmission medium | Copper |

Connection data

Connection technology

| | |
|-------------------|----------------------------|
| Connection method | AS-i penetration technique |
|-------------------|----------------------------|

Connection assignment

| | |
|---|--------------------------------------|
| Contact Color (signal designation) Contact (optional) | 3.1 (AS-i distributors) BN (AS-i+) |
| | 3.2 (AS-i distributors) BU (AS-i-) |
| | 4.1 (AS-i distributors) BK (AUX+) |
| | 4.2 (AS-i distributors) WH (AUX-) |

Interfaces

| | |
|------------|--------------|
| Bus system | AS-Interface |
|------------|--------------|

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Connector

Connection 1

| | |
|---------------------|--|
| Type | Load center lateral AS-i Screw locking |
| Number of positions | 4 |
| Locking type | Screw locking mechanism |
| Material | CuSn (Contact) |
| | Ni/Au (Contact surface) |
| | PBT (Contact carrier) |
| | PBT (Housing) |
| | Stainless steel (Screw connection) |
| Tightening torque | 1.65 Nm (Locking screw) |

SAC-ASI-J-Y-B-PUR-2,0-OE - Distributor



1407581

<https://www.phoenixcontact.com/us/products/1407581>


Connection 2

| | |
|------|----------------|
| Type | free cable end |
|------|----------------|

Cable/line

| | |
|--------------|-----|
| Cable length | 2 m |
|--------------|-----|

PUR halogen-free black [PUR]

| | |
|---------------------------------|--|
| Dimensional drawing |  |
| UL AWM Style | 20549 / 10493 |
| Number of positions | 4 |
| Shielded | no |
| Cable type | PUR halogen-free black [PUR] |
| Conductor structure signal line | 42x 0.10 mm |
| AWG signal line | 22 |
| Conductor cross-section | 4x 0.34 mm ² (Signal line) |
| Wire diameter incl. insulation | 1.25 mm ±0.05 mm |
| External cable diameter | 4.30 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | black |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PP |
| Single wire, color | brown, white, blue, black |
| Overall twist | 4 wires, twisted |
| Ambient temperature (operation) | -40 °C ... 80 °C (fixed routing) -25 °C ... 80 °C (Flexibly installed) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP65 IP67 |
| Ambient temperature (operation) | -25 °C ... 75 °C -25 °C ... 80 °C (Cable, flexible installation) |
| Ambient temperature (operation) (Cable, fixed installation) | -40 °C ... 80 °C (cable, fixed installation) |
| Ambient temperature (storage/transport) | -25 °C ... 85 °C |


Drawings

Dimensional drawing



Distributor, AS-Interface

Dimensional drawing




Distance and position of the mounting holes

1407581

<https://www.phoenixcontact.com/us/products/1407581>

Circuit diagram



Contact assignment of the AS-Interface distributor

1407581

<https://www.phoenixcontact.com/us/products/1407581>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440106 |
| ECLASS-15.0 | 27440106 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002925 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

1407581

<https://www.phoenixcontact.com/us/products/1407581>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | 2-ethylhexyl 10-ethyl-4,4-dioctyl-7-oxo-8-oxa-3,5-dithia-4-stannatetradecanoate (DOTE)(CAS: 15571-58-1) |
| SCIP | 6ffd4317-0cdf-427d-bafe-ea57408e1c72 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 5.629 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com