

SACC-CI-M12MS-5CON-L180THRSHPD - Contact carrier



1409151

<https://www.phoenixcontact.com/us/products/1409151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 5-position, Pin, straight, M12, A-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1409151
Packing unit	60 pc
Minimum order quantity	60 pc
Product key	ABQAGA
GTIN	4046356863124
Weight per piece (including packing)	5.103 g
Weight per piece (excluding packing)	2.608 g
Country of origin	DE

SACC-CI-M12MS-5CON-L180THRSHPD - Contact carrier



1409151

<https://www.phoenixcontact.com/us/products/1409151>

Technical data

Product properties

Product type	Contact insert
Number of positions	5
Shielded	yes
Coding	A
Thread type	M12

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	A

Environmental and real-life conditions

Ambient conditions

UL Type Rating	Type 4 (indoor use only)
----------------	--------------------------

SACC-CI-M12MS-5CON-L180THRSHPD - Contact carrier




1409151

<https://www.phoenixcontact.com/us/products/1409151>

Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

SACC-CI-M12MS-5CON-L180THRSHPD - Contact carrier





1409151


<https://www.phoenixcontact.com/us/products/1409151>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1409151>

 cUL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	22	-

 UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	22	-

 cULus Recognized Approval ID: E221474-20140616				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

SACC-CI-M12MS-5CON-L180THRSHPD - Contact carrier



1409151

<https://www.phoenixcontact.com/us/products/1409151>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12MS-5CON-L180THRSHPD - Contact carrier



1409151

<https://www.phoenixcontact.com/us/products/1409151>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com