

FOC-V14-C1S-S/SJFG - SC-RJ connectors



1407917

<https://www.phoenixcontact.com/us/products/1407917>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SC-RJ connectors, degree of protection: IP65/IP67, number of positions: 2, material: Stainless steel, connection method: Push-Pull, cable outlet: straight

Commercial data

Item number	1407917
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABNOBA
GTIN	4046356782197
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 3.01, Order No. 2252
---------	--

Product properties

Product type	Data plug
Type	Version 14
Number of positions	2
Shielded	no
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Attenuation	≤ 1.5 dB (in accordance with ISO/IEC 24702)
-------------	---

Connection data

Connection method	Push-Pull
-------------------	-----------

Dimensions

Width	22 mm
Height	34 mm
Length	80 mm

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Housing material	Stainless steel

Cable/line

Cable type	Fiber optics
External cable diameter	≤ 10.00 mm (of 5 mm)
Individual wire diameter	2.2 mm
Resistance to oil	yes
Flame resistance	yes

Characteristics

Attenuation	≤ 1.5 dB (in accordance with ISO/IEC 24702)
-------------	---

1407917

<https://www.phoenixcontact.com/us/products/1407917>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Ambient temperature (assembly)	0 °C ... 50 °C
Resistance to oil	yes

Standards and regulations

Flame resistance	yes
Resistance to oil	yes
Standards/specifications	IEC 61076

FOC-V14-C1S-S/SJFG - SC-RJ connectors



1407917

<https://www.phoenixcontact.com/us/products/1407917>

Classifications

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1407917

<https://www.phoenixcontact.com/us/products/1407917>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
-------------------------------------	---

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com