

# SACC-CI-M12MSB-5CON-L180-THRPD - Contact carrier



1409152

<https://www.phoenixcontact.com/us/products/1409152>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 5-position, Pin, straight, M12, B-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Commercial data

Item number	1409152
Packing unit	60 pc
Minimum order quantity	60 pc
Product key	ABQAGM
GTIN	4046356863148
Weight per piece (including packing)	5.06 g
Weight per piece (excluding packing)	2.598 g
Country of origin	DE

# SACC-CI-M12MSB-5CON-L180-THRPD - Contact carrier



1409152

<https://www.phoenixcontact.com/us/products/1409152>

## Technical data

### Product properties

Product type	Contact insert
Number of positions	5
Coding	B
Thread type	M12

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Connector

#### Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	B

### Environmental and real-life conditions

#### Ambient conditions

UL Type Rating	Type 4 (indoor use only)
----------------	--------------------------

# SACC-CI-M12MSB-5CON-L180-THRPD - Contact carrier




1409152

<https://www.phoenixcontact.com/us/products/1409152>

## Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., B-coded, male side

# SACC-CI-M12MSB-5CON-L180-THRPD - Contact carrier





1409152

<https://www.phoenixcontact.com/us/products/1409152>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1409152>

 <b>cUL Recognized</b> Approval ID: E118976-20100522				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	60 V	4 A	22	-

 <b>UL Recognized</b> Approval ID: E118976-20100522				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	60 V	4 A	22	-

# SACC-CI-M12MSB-5CON-L180-THRPD - Contact carrier



1409152

<https://www.phoenixcontact.com/us/products/1409152>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M12MSB-5CON-L180-THRPD - Contact carrier



1409152

<https://www.phoenixcontact.com/us/products/1409152>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)