

FOC-V06-D1PGY-S/SJBE4 - FO coupling



1410050

<https://www.phoenixcontact.com/us/products/1410050>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SC-RJ field coupling

SC-RJ coupling, IP65/67, duplex, can be used for GOF (multi-mode and single-mode), PCF, and polymer fiber types

Your advantages

- Permanent mounting is also an option
- Including covers for protection against environmental influences
- Can be used for all fiber types

Commercial data

Item number	1410050
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABNNBZ
GTIN	4046356892704
Weight per piece (including packing)	39.7 g
Weight per piece (excluding packing)	35.7 g
Country of origin	DE

1410050

<https://www.phoenixcontact.com/us/products/1410050>

Technical data

Product properties

Product type	Female insert
Housing type	Plastic sleeve housing
Type	SC-RJ
Sensor type	Ethernet
Number of positions	2
Connection profile	SCRJ
Number of slots	1
Cable outlet	straight

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated surge voltage	0.8 kV
Nominal current I_N	0.5 A
Transmission medium	FO

Connection data

Connection technology

Connection method	Coupling
-------------------	----------

Dimensions

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Material specifications

Color	gray
Material	Plastic
Flammability rating according to UL 94	V0
Seal material	NBR
Ferrule material	Zirconia ceramics
Housing material	Plastic
Contact material	Copper alloy

Cable/line

FO cable

Number of fibers	2
Fiber type	GOF, PCF, POF

FOC-V06-D1PGY-S/SJBE4 - FO coupling



1410050

<https://www.phoenixcontact.com/us/products/1410050>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP65/IP67
Ambient temperature (operation)	-10 °C ... 60 °C

FOC-V06-D1PGY-S/SJBE4 - FO coupling



1410050

<https://www.phoenixcontact.com/us/products/1410050>

Classifications

ECLASS

ECLASS-13.0

19170116

ETIM

ETIM 9.0

EC000516

UNSPSC

UNSPSC 21.0

39121500

FOC-V06-D1PGY-S/SJBE4 - FO coupling



1410050

<https://www.phoenixcontact.com/us/products/1410050>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com