

# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 2-position, PUR halogen-free, black-gray RAL 7021, Plug straight Superseal Clip locking, coding: A, on Socket straight Superseal Clip locking, cable length: 0.6 m

## Commercial data

Item number	1410759
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF08
Product key	AF1DWA
GTIN	4046356924474
Weight per piece (including packing)	40 g
Weight per piece (excluding packing)	40 g
Customs tariff number	85444290
Country of origin	DE

# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Application	Mobile hydraulics
Number of positions	2
No. of cable outlets	1
Shielded	no
Coding	A

### Material specifications

Flammability rating according to UL 94	HB
Seal material	Silicon
Material of grip body	TPU
Contact material	CuZn (pin)/PhCuSn (socket)
Contact surface material	nickel-plated
Contact carrier material	PA 6.6
Material for screw connection	not available

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	24 V AC
	24 V DC
Nominal current $I_N$	8 A

### Signaling

Status display	no
Status display present	no

### Connector

#### Connection 1

Type	Plug straight Superseal Clip locking
Number of positions	2
Locking type	Clip locking
Coding type	A

#### Connection 2

Type	Socket straight Superseal Clip locking
Number of positions	2
Locking type	Clip locking

### Cable/line


Cable length	0.6 m
--------------	-------

# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable

1410759

<https://www.phoenixcontact.com/us/products/1410759>

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	33 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	2
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.15 mm
AWG signal line	18
Conductor cross-section	2x 0.75 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.69 mm ±0.05 mm (Signal line)
External cable diameter	4.80 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	≥ 0.38 mm
Overall twist	2 wires, twisted
Max. conductor resistance	≤ 26 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V AC
Test voltage	≥ 3000 V AC (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	24 mm
Smallest bending radius, movable installation	48 mm
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 48 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Halogen-free	in accordance with DIN VDE 0472 part 815 in accordance with DIN EN 50267-2-1
Flame resistance	according to UL 758/1581 (horizontal) in accordance with UL 758/1581 FT2 according to DIN EN 60332-2-2
Resistance to oil	According to DIN EN 60811-2-1, 168 h at 100°C

# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

	according to UL 758, 168 h at 60 °C
Other resistance	hydrolysis and microbe resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
	Low adhesion
	abrasion-resistant
Special properties	flexible
	Flexible cable conduit capable
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
	IP69K
Ambient temperature (operation) (male connector/female connector)	-20 °C ... 85 °C (Superseal)

# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

## Drawings

Dimensional drawing



Superseal, plug, view from above and side

Dimensional drawing



Superseal, socket, view from above and side

1410759


<https://www.phoenixcontact.com/us/products/1410759>

Schematic diagram



Super seal plug pin assignment, 2-pos.

Schematic diagram



Super seal socket pin assignment, 2-pos.


# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Circuit diagram



Contact assignment of the super seal plug to the super seal socket

# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1410759>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387

# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)