

# FOC-OE-OE-GZ03/... - FO cable




1411564

<https://www.phoenixcontact.com/us/products/1411564>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fiber optic cable, multi-mode fiberglass 50/125 µm, OM4, length: various



## Your advantages

- Ideal for assembly with fiberglass connectors
- Exceptional fiber quality for reliable data transmission
- Very high data rates possible for demanding applications
- Satisfies UL 94, V0

## Commercial data

Item number	1411564
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB50
Product key	ABNICC
Customs tariff number	85447000
Country of origin	DE

1411564

<https://www.phoenixcontact.com/us/products/1411564>

## Technical data

### Product properties

Product type	Data cable by the meter
Application	Indoor installation
Number of positions	2
No. of conductors	2

### Electrical properties

Attenuation	≤ 2.5 dB/km (with 850 nm)
	≤ 0.7 dB/km (with 1300 nm)
Transmission medium	FO
Transmission speed	10 Gbps

### Dimensions

#### External dimensions

External diameter min.	2 mm
External diameter max.	4.2 mm

### Material specifications

Color	violet
Flammability rating according to UL 94	V0
Outer sheath, material	LSZH

### Connector

#### Connection 2

Type	free cable end
Degree of protection	IP20

### Cable/line

Cable length	2.50 m
Cable weight	8.30 kg/km
Cable type	Fiberglass
Cable type	Zip cord
Cable abbreviation	I-V(ZN)H
External cable diameter	2.00 mm (Zip cord)
Outer sheath, material	LSZH
External sheath, color	violet
Wire diameter incl. insulation	900 µm
Individual wire diameter	900 µm (low-bend)
Single wire, color	-
Smallest bending radius, fixed installation	15 mm
Smallest bending radius, movable installation	30 mm

# FOC-OE-OE-GZ03/... - FO cable



1411564

<https://www.phoenixcontact.com/us/products/1411564>

Tensile strength short-term/long-term	600 N
Cable, attenuation	2.5 dB/km (at 850 nm), 0.7 dB/km (at 1300 nm)
Halogen-free	complying with IEC 60754-1/2
Flame resistance	yes

## FO cable

Number of fibers	2
Fiber	50/125 µm
Fiber type	Multimode fiberglass 50/125 µm
Transmission medium	Multi-mode fiberglass
Wavelength	850, 1300 nm

## Mechanical properties

Tensile strength short-term/long-term	600 N
---------------------------------------	-------

## Mechanical data

Smallest bending radius	30 mm
-------------------------	-------

## Characteristics

Attenuation	≤ 2.5 dB/km (with 850 nm)
-------------	---------------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Resistance to UV radiation	no

## Standards and regulations

Flame resistance	yes
------------------	-----

## Mounting

cable layer type	Indoors
------------------	---------

# FOC-OE-OE-GZ03/... - FO cable



1411564

<https://www.phoenixcontact.com/us/products/1411564>

## Classifications

### ECLASS

ECLASS-15.0	27061803
ECLASS-13.0	27061803

### ETIM

ETIM 10.0	EC000034
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# FOC-OE-OE-GZ03/... - FO cable



1411564

<https://www.phoenixcontact.com/us/products/1411564>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)