

SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 flush-type socket, front mounting

Device connector rear mounting, Ethernet CAT6_A, 8-position, Socket, straight, M12-SPEEDCON, X-coding, Wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1411820
Packing unit	20 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Sales key	AB26
Product key	ABQAIA
GTIN	4046356956376
Weight per piece (including packing)	11.81 g
Weight per piece (excluding packing)	9.736 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting (M12 x 1)
---------------	-------------------------

Product properties

Product type	Circular connectors (device side)
Number of positions	8
Coding	X
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Contact carrier	PPA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	EPDM
Flammability rating according to UL 94	V0

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	< 5 mΩ
Insulation resistance	> 100 MΩ
Nominal voltage U_N	50 V AC
	60 V DC
Nominal current I_N	0.5 A
Transmission characteristics (category)	CAT6 _A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

Mechanical properties

SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	X

Cable/line

Signal type/category	Ethernet CAT6 _A
----------------------	----------------------------

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP67 (When plugged in)
Ambient temperature (operation)	-40 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting

1411820

<https://www.phoenixcontact.com/us/products/1411820>

Drawings



M12 socket pin assignment, 8-pos, view of socket side

SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting





1411820

<https://www.phoenixcontact.com/us/products/1411820>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411820>

 cUL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

 UL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2e6a313b-ab58-4843-8be2-529282446794

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com