

SAC-3P-MR/BI-1L-Z SCO 180 - Valve connector



1409724

<https://www.phoenixcontact.com/us/products/1409724>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Valve connector, 3-position, Plug angled M12, coding: A, on Valve connector BI (11 mm), with 1 LED, Wiring: Z diode, Pin connector pattern of valve plug rotated 180°

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1409724 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF10 |
| Product key | AF1GDA |
| GTIN | 4046356900683 |
| Weight per piece (including packing) | 25.7 g |
| Weight per piece (excluding packing) | 25.7 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

1409724

<https://www.phoenixcontact.com/us/products/1409724>

Technical data

Product properties

| | |
|----------------------|-------------------------|
| Product type | Valve connector adapter |
| Number of positions | 3 |
| No. of cable outlets | 1 |
| Coding | A |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Connection data

| | |
|-------------------|--------------------------|
| Connection method | M12 connector |
| Tightening torque | 0.6 Nm (Valve connector) |

Electrical properties

| | |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 24 V AC |
| | 24 V DC |
| Nominal current I_N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|------------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|------------|

Material specifications

| | |
|--|------------------------------|
| Flammability rating according to UL 94 | HB |
| Seal material | TPU |
| Material housing valve plug | TPU |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | PA 66 |
| Contact material | CuSn |
| Valve plug contact insert material | PA 6.6 |
| Contact surface material | Sn |
| Material for screw connection | Zinc die-cast, nickel-plated |

Signaling

| | |
|------------------------|--------------|
| Status display | LED (yellow) |
| Status display present | yes |

Connector

SAC-3P-MR/BI-1L-Z SCO 180 - Valve connector



1409724

<https://www.phoenixcontact.com/us/products/1409724>

Connection 1

| | |
|---------------------|-----------------|
| Type | Plug angled M12 |
| Number of positions | 3 |
| Coding type | A |

Connection 2

| | |
|---------------------|----------------------------|
| Type | Valve connector BI (11 mm) |
| Number of positions | 3 |
| Material | CuSn (Contact) |
| | Sn (Contact surface) |
| | PA 6.6 (Contact carrier) |
| | TPU (Housing) |
| Protective circuit | Z diode |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------------------------|
| Degree of protection | IP65 |
| | IP67 |
| Ambient temperature (operation) (Valve connector) | -25 °C ... 85 °C (Valve connector) |

Standards and regulations

M12

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |



SAC-3P-MR/BI-1L-Z SCO 180 - Valve connector

1409724

<https://www.phoenixcontact.com/us/products/1409724>

Drawings

Dimensional drawing




as illustrated, but with cable outlet rotated 180°

SAC-3P-MR/BI-1L-Z SCO 180 - Valve connector

1409724


<https://www.phoenixcontact.com/us/products/1409724>

Schematic diagram



Pin assignment M12 plug, 3-pos., A-coded, view male side

Schematic diagram




Valve connector pin assignment, type BI

SAC-3P-MR/BI-1L-Z SCO 180 - Valve connector



1409724

<https://www.phoenixcontact.com/us/products/1409724>



SAC-3P-MR/BI-1L-Z SCO 180 - Valve connector




1409724

<https://www.phoenixcontact.com/us/products/1409724>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1409724>

|  CSAus Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 24 V | 4 A | - | - |

SAC-3P-MR/BI-1L-Z SCO 180 - Valve connector



1409724

<https://www.phoenixcontact.com/us/products/1409724>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440105 |
| ECLASS-15.0 | 27440105 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003623 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

SAC-3P-MR/BI-1L-Z SCO 180 - Valve connector



1409724

<https://www.phoenixcontact.com/us/products/1409724>

Environmental product compliance

EU RoHS

| | |
|---|--------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.63 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com