

SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 2-position, PUR halogen-free, black-gray RAL 7021, Plug straight Superseal Clip locking, coding: A, on Socket straight Superseal Clip locking, cable length: 0.6 m

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1410759 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF08 |
| Product key | AF1DWA |
| GTIN | 4046356924474 |
| Weight per piece (including packing) | 40 g |
| Weight per piece (excluding packing) | 40 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Technical data

Product properties

| | |
|----------------------|-----------------------|
| Product type | Sensor/actuator cable |
| Application | Mobile hydraulics |
| Number of positions | 2 |
| No. of cable outlets | 1 |
| Shielded | no |
| Coding | A |

Material specifications

| | |
|--|----------------------------|
| Flammability rating according to UL 94 | HB |
| Seal material | Silicon |
| Material of grip body | TPU |
| Contact material | CuZn (pin)/PhCuSn (socket) |
| Contact surface material | nickel-plated |
| Contact carrier material | PA 6.6 |
| Material for screw connection | not available |

Electrical properties

| | |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 24 V AC 24 V DC |
| Nominal current I_N | 8 A |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Connector

Connection 1

| | |
|---------------------|--------------------------------------|
| Type | Plug straight Superseal Clip locking |
| Number of positions | 2 |
| Locking type | Clip locking |
| Coding type | A |

Connection 2

| | |
|---------------------|--|
| Type | Socket straight Superseal Clip locking |
| Number of positions | 2 |
| Locking type | Clip locking |

Cable/line


| | |
|--------------|-------|
| Cable length | 0.6 m |
|--------------|-------|

SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable

1410759

<https://www.phoenixcontact.com/us/products/1410759>

PUR halogen-free black [PUR]

| | |
|---|---|
| Dimensional drawing |  |
| Cable weight | 33 kg/km |
| UL AWM Style | 20549 / 10493 (80°C/300 V) |
| Number of positions | 2 |
| Shielded | no |
| Cable type | PUR halogen-free black [PUR] |
| Conductor structure signal line | 42x 0.15 mm |
| AWG signal line | 18 |
| Conductor cross-section | 2x 0.75 mm ² (Signal line) |
| Wire diameter incl. insulation | 1.69 mm ±0.05 mm (Signal line) |
| External cable diameter | 4.80 mm ±0.15 mm |
| Outer sheath, material | PUR |
| External sheath, color | black-gray RAL 7021 |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PP |
| Single wire, color | brown, blue |
| Thickness, insulation | ≥ 0.21 mm |
| Thickness, outer sheath | ≥ 0.38 mm |
| Overall twist | 2 wires, twisted |
| Max. conductor resistance | ≤ 26 Ω/km (at 20 °C) |
| Insulation resistance | ≥ 1 GΩ*km (at 20 °C) |
| Nominal voltage, cable | ≤ 300 V AC |
| Test voltage | ≥ 3000 V AC (Spark test) |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 10 x D |
| Smallest bending radius, fixed installation | 24 mm |
| Smallest bending radius, movable installation | 48 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 4000000, Bending radius: 48 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ² |
| Halogen-free | in accordance with DIN VDE 0472 part 815 in accordance with DIN EN 50267-2-1 |
| Flame resistance | according to UL 758/1581 (horizontal) in accordance with UL 758/1581 FT2 according to DIN EN 60332-2-2 |
| Resistance to oil | According to DIN EN 60811-2-1, 168 h at 100°C |

SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

| | |
|---------------------------------|--|
| | according to UL 758, 168 h at 60 °C |
| Other resistance | hydrolysis and microbe resistant |
| | partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) |
| | Low adhesion |
| | abrasion-resistant |
| Special properties | flexible |
| | Flexible cable conduit capable |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation) |
| | -25 °C ... 80 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------------------|
| Degree of protection | IP67 |
| | IP69K |
| Ambient temperature (operation) (male connector/female connector) | -20 °C ... 85 °C (Superseal) |

SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Drawings

Dimensional drawing



Superseal, plug, view from above and side

Dimensional drawing



Superseal, socket, view from above and side

1410759

<https://www.phoenixcontact.com/us/products/1410759>

Schematic diagram



Super seal plug pin assignment, 2-pos.

Schematic diagram



Super seal socket pin assignment, 2-pos.


SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Circuit diagram



Contact assignment of the super seal plug to the super seal socket

SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1410759>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-2P-SUSMS/ 0,6-PUR/SUSFS - Sensor/actuator cable



1410759

<https://www.phoenixcontact.com/us/products/1410759>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com