

# SACC-CIP-M8FSB-5P SMD SH T - Contact carrier



1412237

<https://www.phoenixcontact.com/us/products/1412237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Universal, 5-position, Socket, straight, M8, B-coding, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Optional shield connection and seal for the device when not plugged in

## Commercial data

Item number	1412237
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB22
Product key	ABQHCG
GTIN	4046356988797
Weight per piece (including packing)	3.125 g
Weight per piece (excluding packing)	2.321 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Data, signals
Sensor type	Universal
Number of positions	5
No. of control contacts	5
Seal present	yes
Shielded	yes
Coding	B
Thread type	M8

### Insulation characteristics

Overvoltage category	III
----------------------	-----

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\leq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	3 A

### Connection data

Connection method	SMD reflow
-------------------	------------

### Interfaces

Bus system	DeviceNet™
Signal type/category	Universal

### Material specifications

Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM
Flammability rating according to UL 94	V0

### Connector

# SACC-CIP-M8FSB-5P SMD SH T - Contact carrier



1412237

<https://www.phoenixcontact.com/us/products/1412237>

## Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	B

## Cable/line

Signal type/category	Universal
----------------------	-----------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)

## Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

## Packaging specifications

Type of packaging	Tray
-------------------	------


# SACC-CIP-M8FSB-5P SMD SH T - Contact carrier

1412237

<https://www.phoenixcontact.com/us/products/1412237>

## Drawings

Schematic diagram



Pin assignment of M8 socket, 5-pos., B-coded

# SACC-CIP-M8FSB-5P SMD SH T - Contact carrier




1412237

<https://www.phoenixcontact.com/us/products/1412237>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412237>

 <b>cULus Recognized</b> Approval ID: E221474-20160506				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	3 A	-	-

# SACC-CIP-M8FSB-5P SMD SH T - Contact carrier



1412237

<https://www.phoenixcontact.com/us/products/1412237>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CIP-M8FSB-5P SMD SH T - Contact carrier



1412237

<https://www.phoenixcontact.com/us/products/1412237>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)