

# SACC-CI-M8FS-3P SMD R32 - Contact carrier



1412243

<https://www.phoenixcontact.com/us/products/1412243>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 3-position, Socket, straight, M8, A-coding, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Optional shield connection and seal for the device when not plugged in

## Commercial data

Item number	1412243
Packing unit	120 pc
Minimum order quantity	120 pc
Sales key	AB22
Product key	ABQHCT
GTIN	4046356988841
Weight per piece (including packing)	4.78 g
Weight per piece (excluding packing)	1.9 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Signal
Number of positions	3
No. of control contacts	3
Seal present	no
Shielded	no
Coding	A
Thread type	M8

### Insulation characteristics

Overvoltage category	III
----------------------	-----

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A

### Connection data

Connection method	SMD reflow
-------------------	------------

### Material specifications

Flammability rating according to UL 94	V0
--	----

### Connector

#### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	A

### Environmental and real-life conditions

#### Ambient conditions

# SACC-CI-M8FS-3P SMD R32 - Contact carrier



1412243

<https://www.phoenixcontact.com/us/products/1412243>

Degree of protection	IP67 (correctly plugged in and locked)
----------------------	--

## Packaging specifications

Type of packaging	Belt
-------------------	------

# SACC-CI-M8FS-3P SMD R32 - Contact carrier


1412243

<https://www.phoenixcontact.com/us/products/1412243>



## Drawings

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

# SACC-CI-M8FS-3P SMD R32 - Contact carrier




1412243

<https://www.phoenixcontact.com/us/products/1412243>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412243>

 <b>cULus Recognized</b> Approval ID: E221474-20160506				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	60 V	4 A	-	-

# SACC-CI-M8FS-3P SMD R32 - Contact carrier



1412243

<https://www.phoenixcontact.com/us/products/1412243>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M8FS-3P SMD R32 - Contact carrier



1412243

<https://www.phoenixcontact.com/us/products/1412243>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)