

FOC-OE-OE-GZ04/... - FO cable




1411566

<https://www.phoenixcontact.com/us/products/1411566>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fiber optic cable, multi-mode fiberglass 62.5/125 µm, OM1, length: various



Your advantages

- Ideal for assembly with fiberglass connectors
- Exceptional fiber quality for reliable data transmission
- Very high data rates possible for demanding applications
- Satisfies UL 94, V0

Commercial data

Item number	1411566
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB50
Product key	ABNICC
Customs tariff number	85447000
Country of origin	DE

1411566

<https://www.phoenixcontact.com/us/products/1411566>

Technical data

Product properties

Product type	Data cable by the meter
Application	Indoor installation
Number of positions	2
No. of conductors	2

Electrical properties

Attenuation	≤ 3 dB/km (with 850 nm)
	≤ 0.8 dB/km (with 1300 nm)
Transmission medium	FO
Transmission speed	1 Gbps

Dimensions

External dimensions

External diameter min.	2 mm
External diameter max.	4.2 mm

Material specifications

Color	orange
Flammability rating according to UL 94	V0
Outer sheath, material	LSZH

Connector

Connection 2

Type	free cable end
Degree of protection	IP20

Cable/line

Cable length	2.50 m
Cable weight	8.30 kg/km
Cable type	Fiberglass
Cable type	Zip cord
Cable abbreviation	I-V(ZN)H
External cable diameter	2.00 mm (Zip cord)
Outer sheath, material	LSZH
External sheath, color	orange
Individual wire diameter	900 µm
Single wire, color	-
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm
Tensile strength short-term/long-term	600 N

FOC-OE-OE-GZ04/... - FO cable



1411566

<https://www.phoenixcontact.com/us/products/1411566>

Cable, attenuation	3.2 dB/km (at 850 nm); 0.9 dB/km (at 1300 nm)
Halogen-free	According to IEC 60754-2
Flame resistance	yes

FO cable

Number of fibers	2
Fiber	62.5/125 µm
Fiber type	Multimode fiberglass 62.5/125 µm
Transmission medium	Multi-mode fiberglass
Wavelength	850, 1300 nm

Mechanical properties

Tensile strength short-term/long-term	600 N
---------------------------------------	-------

Mechanical data

Smallest bending radius	30 mm
-------------------------	-------

Characteristics

Attenuation	≤ 3 dB/km (with 850 nm)
-------------	-------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 50 °C

Standards and regulations

Flame resistance	yes
------------------	-----

Mounting

cable layer type	Indoors
------------------	---------

FOC-OE-OE-GZ04/... - FO cable



1411566

<https://www.phoenixcontact.com/us/products/1411566>

Classifications

ECLASS

ECLASS-13.0	27061803
ECLASS-15.0	27061803

ETIM

ETIM 10.0	EC000034
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FOC-OE-OE-GZ04/... - FO cable



1411566

<https://www.phoenixcontact.com/us/products/1411566>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com