

# NBC-M12FSBP-PG9/5,0-94D/R4AQ - Network cable



1413001

<https://www.phoenixcontact.com/us/products/1413001>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, cable length: 5 m, number of positions: 8, 1 Gbps, Ethernet, 4x2xAWG26/7, SF/UTP, black RAL 9005

## Your advantages

- Perfect for industrial applications
- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Compact angle

## Commercial data

Item number	1413001
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB18
Product key	ABNPAA
GTIN	4046356980555
Weight per piece (including packing)	293.3 g
Weight per piece (excluding packing)	280.7 g
Customs tariff number	85444290
Country of origin	PL

1413001

<https://www.phoenixcontact.com/us/products/1413001>

## Technical data

### Product properties

Product type	Circular connectors (device side)
Sensor type	Ethernet
Number of positions	8
Shielded	yes

### Insulation characteristics

Degree of pollution	3
---------------------	---

### Material specifications

Flammability rating according to UL 94	V2
--	----

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

### Connector

#### Connection 1

Type	Flush-type female connector straight M12
Coding type	A
Degree of protection	IP65/IP67


#### Connection 2

Type	Plug straight RJ45
Degree of protection	IP20

### Cable/line

Cable length	5.00 m
--------------	--------

### Ethernet [94D]

Dimensional drawing	
UL AWM Style	2464 (80°C/300 V)
Number of positions	8

# NBC-M12FSBP-PG9/5,0-94D/R4AQ - Network cable



1413001

<https://www.phoenixcontact.com/us/products/1413001>

Shielded	yes
Cable type	Ethernet [94D]
Conductor structure	4x2xAWG26/7, SF/UTP
Signal speed	0.6 c
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	4x 2x 0.14 mm <sup>2</sup>
Wire diameter incl. insulation	0.98 mm ±0.05 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PVC (reinforced) UV-resistant
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Thickness, outer sheath	0.80 mm
Twisted pairs	2 cores to the pair
Overall twist	4 pairs, twisted
Optical shield covering	85 %
Max. conductor resistance	< 140 Ω/km
Insulation resistance	≥ 5 GΩ*km
Wave impedance	100 Ω ±15 Ω (at 4 ... 100 MHz)
Cable capacity	< 56 nF/km
Nominal voltage, cable	72 V DC 300 V AC
Test voltage Core/Core	2500 V DC (2 s)
Test voltage Core/Shield	2500.00 V DC (2 s)
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm
Tensile strength	80 N
Flame resistance	According to VW-1
Resistance to oil	according to IEC 60811-2-1
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (installation)	0 °C ... 50 °C

1413001

<https://www.phoenixcontact.com/us/products/1413001>

## Classifications

### ECLASS

ECLASS-13.0	27060308
ECLASS-15.0	27440103

### ETIM

ETIM 9.0	EC001262
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1413001

<https://www.phoenixcontact.com/us/products/1413001>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)