

# SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 flush-type socket, front mounting

Device connector rear mounting, Ethernet CAT6<sub>A</sub>, 8-position, Socket, straight, M12-SPEEDCON, X-coding, Wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1411820
Packing unit	20 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Sales key	AB26
Product key	ABQAIA
GTIN	4046356956376
Weight per piece (including packing)	11.81 g
Weight per piece (excluding packing)	9.736 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

## Technical data

### Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

### Mounting

Mounting type	Rear mounting (M12 x 1)
---------------	-------------------------

### Product properties

Product type	Circular connectors (device side)
Number of positions	8
Coding	X
Thread type	M12

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Contact carrier	PPA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	EPDM
Flammability rating according to UL 94	V0

### Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	< 5 mΩ
Insulation resistance	> 100 MΩ
Nominal voltage $U_N$	50 V AC
	60 V DC
Nominal current $I_N$	0.5 A
Transmission characteristics (category)	CAT6 <sub>A</sub>

### Connection data

Conductor connection	
Connection method	Wave soldering
Contact connection type	Socket

### Mechanical properties

# SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

## Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

## Connector

### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	X

## Cable/line

Signal type/category	Ethernet CAT6 <sub>A</sub>
----------------------	----------------------------

## Environmental and real-life conditions

### Ambient conditions


Degree of protection	IP67 (When plugged in)
Ambient temperature (operation)	-40 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

# SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting

1411820

<https://www.phoenixcontact.com/us/products/1411820>

## Drawings



M12 socket pin assignment, 8-pos, view of socket side

# SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting





1411820

<https://www.phoenixcontact.com/us/products/1411820>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411820>

 <b>cUL Recognized</b> Approval ID: E335024-20120308				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	60 V	0.5 A	-	-

 <b>UL Recognized</b> Approval ID: E335024-20120308				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	60 V	0.5 A	-	-

# SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 10.0	EC003568
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSIV-FSX-8CON-L180 SCO - Device connector rear mounting



1411820

<https://www.phoenixcontact.com/us/products/1411820>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2e6a313b-ab58-4843-8be2-529282446794

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)