

# SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/us/products/1413446>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Ethernet CAT6<sub>A</sub>, 8-position, Socket, straight, M12, X-coding, THR solder connection, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

## Commercial data

Item number	1413446
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB23
Product key	ABQAGT
GTIN	4046356999083
Weight per piece (including packing)	7.365 g
Weight per piece (excluding packing)	3.329 g
Customs tariff number	85366990
Country of origin	DE

# SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/us/products/1413446>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Data
Sensor type	Ethernet
Number of positions	8
Seal present	no
Shielded	yes
Coding	X
Thread type	M12

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	< 5 mΩ
Insulation resistance	> 100 MΩ
Nominal voltage $U_N$	50 V AC
	60 V DC
Nominal current $I_N$	0.5 A
Transmission characteristics (category)	CAT6 <sub>A</sub>

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Interfaces

Signal type/category	Ethernet CAT6 <sub>A</sub>
----------------------	----------------------------

### Material specifications

Material Contact carrier	PA 6T/66
Material Contact	CuZn
Material Contact surface	Ni/Au
Flammability rating according to UL 94	V0

### Connector

# SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/us/products/1413446>

## Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	X

## Cable/line

Signal type/category	Ethernet CAT6 <sub>A</sub>
----------------------	----------------------------

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 95 °C
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-109

## Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad


# SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/us/products/1413446>

## Drawings



Pin assignment M12 connector, 8-pos., view socket side

# SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/us/products/1413446>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1413446>

 <b>cUL Recognized</b> Approval ID: E335024-20120308				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	60 V	0.5 A	-	-

 <b>UL Recognized</b> Approval ID: E335024-20120308				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	60 V	0.5 A	-	-

# SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/us/products/1413446>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M12FSX-8CON-L180 TOR32 - Contact carrier



1413446

<https://www.phoenixcontact.com/us/products/1413446>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)