

# SACC-CIP-M12MS-8P SMD T - Contact carrier



1411945

<https://www.phoenixcontact.com/us/products/1411945>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 8-position, Pin, straight, M12, A-coding, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

## Commercial data

Item number	1411945
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB23
Product key	ABQBGM
GTIN	4046356990714
Weight per piece (including packing)	4.468 g
Weight per piece (excluding packing)	3.726 g
Customs tariff number	85366990
Country of origin	DE

1411945

<https://www.phoenixcontact.com/us/products/1411945>

## Technical data

### Product properties

Product type	Contact insert
Application	Signal
Number of positions	8
No. of control contacts	8
Seal present	yes
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V
Nominal current $I_N$	2 A

### Connection data

Connection method	SMD reflow
-------------------	------------

### Material specifications

Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM
Flammability rating according to UL 94	V0

### Connector

#### Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	A

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

1411945

<https://www.phoenixcontact.com/us/products/1411945>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 105 °C -55 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

## Packaging specifications

Type of packaging	Tray
Delivery state	with assembly pad

# SACC-CIP-M12MS-8P SMD T - Contact carrier

1411945

<https://www.phoenixcontact.com/us/products/1411945>



## Drawings

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side

# SACC-CIP-M12MS-8P SMD T - Contact carrier



1411945

<https://www.phoenixcontact.com/us/products/1411945>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411945>

 <b>cULus Recognized</b> Approval ID: E221474-20160506				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	2 A	-	-

# SACC-CIP-M12MS-8P SMD T - Contact carrier



1411945

<https://www.phoenixcontact.com/us/products/1411945>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CIP-M12MS-8P SMD T - Contact carrier



1411945

<https://www.phoenixcontact.com/us/products/1411945>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)