

SACC-CIM12MS17PL180THRSHSAMPLE - Contact carrier



1413555

<https://www.phoenixcontact.com/us/products/1413555>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 17-position, Pin, straight, M12, A-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1413555
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABQAGA
GTIN	4055626008257
Weight per piece (including packing)	5.7 g
Weight per piece (excluding packing)	3.436 g
Country of origin	DE

SACC-CIM12MS17PL180THRSHSAMPLE - Contact carrier



1413555

<https://www.phoenixcontact.com/us/products/1413555>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Number of positions	17
No. of cable outlets	1
Shielded	yes
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	1.5 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Signaling

Status display	no
Status display present	no

Material specifications

Material Contact carrier	PPA
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	V0

Connector

Connection 1

Head design	Pin
-------------	-----

SACC-CIM12MS17PL180THRSHSAMPLE - Contact carrier



1413555

<https://www.phoenixcontact.com/us/products/1413555>

Head cable outlet	straight
Head thread type	M12
Coding	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C -40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

SACC-CIM12MS17PL180THRSHSAMPLE - Contact carrier




1413555

<https://www.phoenixcontact.com/us/products/1413555>

Drawings

Schematic diagram



Pin assignment M12 male connector, 17-pos., male side view

SACC-CIM12MS17PL180THRSHSAMPLE - Contact carrier




1413555

<https://www.phoenixcontact.com/us/products/1413555>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1413555>

 cULus Recognized Approval ID: E221474-20140616				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	1.5 A	-	-

SACC-CIM12MS17PL180THRSHSAMPLE - Contact carrier



1413555

<https://www.phoenixcontact.com/us/products/1413555>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CIM12MS17PL180THRSHSAMPLE - Contact carrier



1413555

<https://www.phoenixcontact.com/us/products/1413555>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com