

# HC-B-TA-PG29-ER-AL - Adapter

1414263

<https://www.phoenixcontact.com/us/products/1414263>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter, aluminum, for EVO housing, Pg29 thread



## Commercial data

Item number	1414263
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	AF7APM
GTIN	4055626022253
Weight per piece (including packing)	84.1 g
Weight per piece (excluding packing)	84.1 g
Customs tariff number	85389099
Country of origin	DE

# HC-B-TA-PG29-ER-AL - Adapter

1414263

<https://www.phoenixcontact.com/us/products/1414263>

## Technical data


### Product properties

Product type	Thread adapter
Application	Bayonet B - Pg
Type of the screw connection	Pg29

### Connection data

Tightening torque	... 10 Nm
-------------------	-----------

### Dimensions

Dimensional drawing	
Thread type on seal side	Pg29

### Internal dimensions

Length of internal thread	13 mm
---------------------------	-------

### Material specifications

Color	aluminum color
Material	Die-cast aluminum, corrosion-resistant
Seal material O-ring	NBR
Housing material	Die-cast aluminum, corrosion resistant

### Mechanical properties

#### Mechanical data

Type of the screw connection	Pg29
------------------------------	------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-B-TA-PG29-ER-AL - Adapter



1414263

<https://www.phoenixcontact.com/us/products/1414263>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-B-TA-PG29-ER-AL - Adapter



1414263

<https://www.phoenixcontact.com/us/products/1414263>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414263>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-B-TA-PG29-ER-AL - Adapter



1414263

<https://www.phoenixcontact.com/us/products/1414263>

## Classifications

### ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

### ETIM

ETIM 10.0	EC000441
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-B-TA-PG29-ER-AL - Adapter



1414263

<https://www.phoenixcontact.com/us/products/1414263>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)