# HC-M-04-CT-M - Contact insert module

1414362

https://www.phoenixcontact.com/us/products/1414362

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 4, power contacts: 4, control contacts: 0, Pin, Crimp connection, 690 V, 40 A, 1.5 $mm^2$ ... 6 $mm^2$, application: Power

## Commercial data

| | |
|---|---|
| Item number | 1414362 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF62 |
| Product key | AF7ACE |
| GTIN | 4055626025056 |
| Weight per piece (including packing) | 11.94 g |
| Weight per piece (excluding packing) | 11.7 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

## Technical data

### Notes

| | |
|---|---|
| General | For HEAVYCON HC-B6 to B48 housing, HC-M-B...-MF-... module carrier frame required, crimp connection, crimp contacts not supplied as standard. |
| General | Connectors may be operated only when there is no load/voltage. |

### Mounting

| | |
|---|---|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
| | The module cannot be used simultaneously with the HC-B..-TMB-SD-IP65 and HC-B..-TMS-SD-IP65 protective covers. |

### Product properties

| | |
|---|---|
| Product type | Modular contact insert |
| Series | HC-M-04 |
| Application | Power |
| Number of positions | 4 |
| Connection profile | 4 |
| Contact numbering | 1 - 4 |
| Number of module slots | 1 |
| No. of power contacts | 4 |
| No. of control contacts | 0 |
| Contact material type | turned |

#### Insulation characteristics

| | |
|---|---|
| Overvoltage category | III |
| Degree of pollution | 3 |

### Connection data


#### Connection technology

| | |
|---|---|
| Connection technology | Crimp connection |
| Connection in acc. with standard | IEC / EN |

#### Conductor connection

| | |
|---|---|
| Conductor cross-section | 1.5 mm² ... 6 mm² |
| Connection cross section AWG | 16 ... 10 |
| Stripping length of the individual wire | 9 mm (9.6 mm (4-6 mm²)) |
| | 14 mm (4 ... 6 mm²) |

### Dimensions

| | |
|---|---|
| Dimensional drawing |   |
| Width | 34.2 mm |
| Height | 44.6 mm |
| Length | 14.6 mm |

Mechanical characteristics

| | |
|---|---|
| Minimum housing height | 52 mm |
| Contact diameter | 4 mm |

## Electrical properties

| | |
|---|---|
| Rated voltage (III/2) contacts | 1000 V |
| Rated voltage (III/3) | 690 V |
| Rated surge voltage (III/2) | 8 kV |
| Rated surge voltage (III/3) | 6 kV |
| Rated surge voltage | 6 kV |
| Rated current | 40 A |
| SCCR | 5 kA (UL 2237) |

## Mechanical properties

Mechanical data

| | |
|---|---|
| Insertion/withdrawal cycles | ≥ 500 |

## Material specifications

| | |
|---|---|
| Flammability rating according to UL 94 | V0 |
| Contact material | Copper alloy |
| Contact surface material | Ag |
| Contact carrier material | PC |

## Environmental and real-life conditions

Ambient conditions


| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 125 °C |

## Standards and regulations

| | |
|---|---|
| Standards/regulations | PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |


## Drawings

Dimensional drawing





Male insert

Schematic diagram




Connector pin assignment, connection side

Diagram




Derating diagram

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1414362

**DNV**
Approval ID: TAE000037S

**CSA**
Approval ID: 158887

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 830 V | 30 A | - 10 | - |

**UL Recognized**
Approval ID: E118976

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 600 V | 37 A | - 10 | - |

**UL Recognized**
Approval ID: E468743

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 600 V | 37 A | - | - |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440217 |
| ECLASS-15.0 | 27440217 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000438 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.068 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com