

HC-M-04-CT-F - Contact insert module



1414363

<https://www.phoenixcontact.com/us/products/1414363>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 4, power contacts: 4, control contacts: 0, Socket, Crimp connection, 690 V, 40 A, 1.5 mm² ... 6 mm², application: Power

Commercial data

Item number	1414363
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
GTIN	4055626025063
Weight per piece (including packing)	9.7 g
Weight per piece (excluding packing)	9.62 g
Customs tariff number	85389099
Country of origin	PL

HC-M-04-CT-F - Contact insert module



1414363

<https://www.phoenixcontact.com/us/products/1414363>

Technical data

Notes

General	For HEAVYCON HC-B6 to B48 housing, HC-M-B...-MF-... module carrier frame required, crimp connection, crimp contacts not supplied as standard.
General	Connectors may be operated only when there is no load/voltage.

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
	The module cannot be used simultaneously with the HC-B..-TMB-SD-IP65 and HC-B..-TMS-SD-IP65 protective covers.

Product properties

Product type	Modular contact insert
Series	HC-M-04
Application	Power
Number of positions	4
Connection profile	4
Contact numbering	1 - 4
Number of module slots	1
No. of power contacts	4
No. of control contacts	0
Contact material type	turned

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data

Connection technology

Connection technology	Crimp connection
Connection in acc. with standard	IEC / EN

Conductor connection


Conductor cross-section	1.5 mm ² ... 6 mm ²
Connection cross section AWG	16 ... 10
Stripping length of the individual wire	9 mm (9.6 mm (4-6 mm ²))
	14 mm (4 ... 6 mm ²)

Dimensions

HC-M-04-CT-F - Contact insert module

1414363

<https://www.phoenixcontact.com/us/products/1414363>

Dimensional drawing	
Width	34.2 mm
Height	40.9 mm
Length	14.6 mm

Mechanical characteristics	
Minimum housing height	52 mm
Contact diameter	4 mm

Electrical properties

Rated voltage (III/2) contacts	1000 V
Rated voltage (III/3)	690 V
Rated surge voltage (III/2)	8 kV
Rated surge voltage (III/3)	6 kV
Rated surge voltage	6 kV
Rated current	40 A
SCCR	5 kA (UL 2237)

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Standards/regulations	PC

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

Standards and regulations

Testing	
Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)

HC-M-04-CT-F - Contact insert module





1414363

<https://www.phoenixcontact.com/us/products/1414363>

Drawings

Dimensional drawing



Female insert


HC-M-04-CT-F - Contact insert module

1414363

<https://www.phoenixcontact.com/us/products/1414363>




Schematic diagram



Connector pin assignment, connection side

1414363

<https://www.phoenixcontact.com/us/products/1414363>



Derating diagram

HC-M-04-CT-F - Contact insert module



1414363

<https://www.phoenixcontact.com/us/products/1414363>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414363>

DNV

Approval ID: TAE000037S



CSA

Approval ID: 158887

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	830 V	30 A	- 10	-



UL Recognized

Approval ID: E118976

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	37 A	- 10	-



UL Recognized

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	37 A	-	-

HC-M-04-CT-F - Contact insert module



1414363

<https://www.phoenixcontact.com/us/products/1414363>

Classifications

ECLASS

ECLASS-13.0	27440217
ECLASS-15.0	27440217

ETIM

ETIM 10.0	EC000438
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-M-04-CT-F - Contact insert module



1414363

<https://www.phoenixcontact.com/us/products/1414363>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.06 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com