

HC-B-GTRS-M20-ER-AL - Cable gland



1414656

<https://www.phoenixcontact.com/us/products/1414656>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Set consisting of: EVO metal adapter 1414256 and metal screw connection with terminal block 1415192, M20

Commercial data

Item number	1414656
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	AF7APM
GTIN	4055626031071
Weight per piece (including packing)	184 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85389099
Country of origin	DE

HC-B-GTRS-M20-ER-AL - Cable gland



1414656

<https://www.phoenixcontact.com/us/products/1414656>

Technical data

Product properties

Product type	Cable screw gland
No. of conductors	1
Type of the screw connection	M20
Shielded	no

Dimensions

Dimensional drawing	
Wrench size, union nut	24 mm
Wrench size, support	24 mm

Material specifications

Color	brass color
Material Pressure screw	Brass, nickel-plated
Seal material	EPDM
Seal material O-ring	NBR
Material for screw connection	Brass, nickel-plated

Cable/line

External cable diameter Cable 1	6 mm ... 13 mm
---------------------------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Ambient temperature (operation)	-40 °C ... 100 °C

HC-B-GTRS-M20-ER-AL - Cable gland


1414656

<https://www.phoenixcontact.com/us/products/1414656>



Drawings

Dimensional drawing



Dimensional drawing

HC-B-GTRS-M20-ER-AL - Cable gland



1414656

<https://www.phoenixcontact.com/us/products/1414656>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414656>



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

HC-B-GTRS-M20-ER-AL - Cable gland



1414656

<https://www.phoenixcontact.com/us/products/1414656>

Classifications

ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

ETIM

ETIM 10.0	EC000441
-----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	940e6fd1-ae41-4e60-b508-80b63dd4a38d

EF3.1 Climate Change

CO2e kg	1.704 kg CO2e
---------	---------------