

SACC-CI-M8FS-3P SMD T - Contact carrier



1412220

<https://www.phoenixcontact.com/us/products/1412220>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 3-position, Socket, straight, M8, A-coding, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Optional shield connection and seal for the device when not plugged in

Commercial data

Item number	1412220
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB22
Product key	ABQHCS
GTIN	4046356988308
Weight per piece (including packing)	2.733 g
Weight per piece (excluding packing)	1.9 g
Customs tariff number	85366990
Country of origin	DE

1412220

<https://www.phoenixcontact.com/us/products/1412220>

Technical data

Product properties

Product type	Contact insert
Application	Signal
Number of positions	3
No. of control contacts	3
Seal present	no
Shielded	no
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Connection data

Connection method	SMD reflow
-------------------	------------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
----------------------	------------------------

SACC-CI-M8FS-3P SMD T - Contact carrier



1412220

<https://www.phoenixcontact.com/us/products/1412220>

Packaging specifications

Type of packaging	Tray
-------------------	------

SACC-CI-M8FS-3P SMD T - Contact carrier


1412220

<https://www.phoenixcontact.com/us/products/1412220>



Drawings

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

SACC-CI-M8FS-3P SMD T - Contact carrier



1412220

<https://www.phoenixcontact.com/us/products/1412220>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412220>

 cULus Recognized Approval ID: E221474-20160506				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

SACC-CI-M8FS-3P SMD T - Contact carrier



1412220

<https://www.phoenixcontact.com/us/products/1412220>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M8FS-3P SMD T - Contact carrier



1412220

<https://www.phoenixcontact.com/us/products/1412220>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com