

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable



1412368

<https://www.phoenixcontact.com/us/products/1412368>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR halogen-free, irradiated, welding sputter-resistant, orange RAL 2003, Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 0.2 m

As shown in the illustration but with an orange conductor

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1412368 |
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Product key | AF1CCA |
| GTIN | 4046356959018 |
| Weight per piece (including packing) | 26.1 g |
| Weight per piece (excluding packing) | 26.1 g |
| Country of origin | PL |

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable



1412368

<https://www.phoenixcontact.com/us/products/1412368>

Technical data

Product properties

| | |
|----------------------|-----------------------|
| Product type | Sensor/actuator cable |
| Number of positions | 4 |
| No. of cable outlets | 1 |
| Shielded | no |
| Coding | A |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | HB |
| Seal material | NBR |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | TPU GF |
| Material for screw connection | Zinc die-cast, nickel-plated |

Electrical properties

| | |
|-----------------------|----------|
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U_N | 250 V AC |
| | 250 V DC |
| Nominal current I_N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Connector

Connection 1

| | |
|---------------------|-------------------|
| Type | Plug straight M12 |
| Number of positions | 4 |
| Coding type | A |

Connection 2

| | |
|------|---------------------|
| Type | Socket straight M12 |
|------|---------------------|

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable

1412368


<https://www.phoenixcontact.com/us/products/1412368>

| | |
|---------------------|---|
| Number of positions | 4 |
| Coding type | A |

Cable/line

| | |
|--------------|-------|
| Cable length | 0.2 m |
|--------------|-------|

PUR irradiated halogen-free orange [150]

| | |
|---|--|
| Dimensional drawing |  |
| Number of positions | 4 |
| Shielded | no |
| Cable type | PUR irradiated halogen-free orange [150] |
| Conductor structure signal line | 19x 0.15 mm |
| AWG signal line | 22 |
| Conductor cross-section | 4x 0.34 mm ² (Signal line) |
| Wire diameter incl. insulation | 1.05 mm ±0.05 mm (Signal line) |
| External cable diameter | 5.20 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | orange RAL 2003 |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PE |
| Single wire, color | brown, white, blue, black |
| Overall twist | 4 wires, twisted |
| Length of twist, overall twist | 27 mm |
| Max. conductor resistance | max. 57 Ω/km |
| Nominal voltage, cable | 320 V (AC) |
| Test voltage | 2500 V (50 Hz, 5 minutes) |
| Smallest bending radius, fixed installation | min. 15 mm |
| Smallest bending radius, movable installation | min. 30 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000000, Bending radius: 52 mm, Traversing path: 10 m, Traversing rate: 3 m/s |
| Dynamic load capacity (torsion) | Torsion: ±360 °/m |
| Halogen-free | The cable is halogen-free |
| Other resistance | hydrolysis and microbe resistant Resistant to welding splashes |
| Special properties | Silicone-free Irradiated |
| Ambient temperature (operation) | -50 °C ... 105 °C (cable, fixed installation) |

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable



1412368

<https://www.phoenixcontact.com/us/products/1412368>

| | |
|--|--|
| | -40 °C ... 105 °C (Cable, flexible installation) |
|--|--|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|--|
| Degree of protection | IP65 |
| | IP68 |
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket) |
| | -50 °C ... 105 °C (cable, fixed installation) |
| | -40 °C ... 105 °C (Cable, flexible installation) |

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable

1412368

<https://www.phoenixcontact.com/us/products/1412368>

Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, straight

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable

1412368

<https://www.phoenixcontact.com/us/products/1412368>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable

1412368

<https://www.phoenixcontact.com/us/products/1412368>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable



1412368

<https://www.phoenixcontact.com/us/products/1412368>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

SAC-4P-M12MS/0,2-150/M12FS 3X4 - Sensor/actuator cable



1412368

<https://www.phoenixcontact.com/us/products/1412368>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com