

SACC-FP-M-M8/M10 SMD - Housing screw connection



1412502

<https://www.phoenixcontact.com/us/products/1412502>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Pin, M8-Screw locking mechanism, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Efficient PCB assembly: two-piece connectors for SMT soldering

Commercial data

Item number	1412502
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB22
Product key	ABQHAB
GTIN	4046356989084
Weight per piece (including packing)	4.4 g
Weight per piece (excluding packing)	4.238 g
Customs tariff number	74198090
Country of origin	DE

SACC-FP-M-M8/M10 SMD - Housing screw connection



1412502

<https://www.phoenixcontact.com/us/products/1412502>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Circular connector housing
Thread type	M8

Connection data

Tightening torque	2 ... 3 Nm
-------------------	------------

Material specifications

Material	Brass, nickel-plated
Seal material	FKM
	FKM
Material for screw connection	Brass, nickel-plated

Connector

Connection 1

Head design	Pin
Head thread type	M8
Head locking type	Screw locking mechanism

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when in locked state
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

Mounting

Mounting type	Front mounting (M10 x 0,75)
---------------	-----------------------------

SACC-FP-M-M8/M10 SMD - Housing screw connection



1412502

<https://www.phoenixcontact.com/us/products/1412502>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 10.0	EC003556
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

SACC-FP-M-M8/M10 SMD - Housing screw connection



1412502

<https://www.phoenixcontact.com/us/products/1412502>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	815666f9-e4c3-4eec-9534-8bab261a2709

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com