

# CUC-PP-MODUL-RJ45:6-RJ45:6/2 - RJ45 connector



1412898

<https://www.phoenixcontact.com/us/products/1412898>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Module, RJ45 to RJ45, consisting of two housings each with 6 x RJ45 10 Gbps (Class E<sub>A</sub> pre-assembled with multi-cable, length: 2 m, GHMT-certified.



## Product description

Module, RJ45 to RJ45, consisting of two housings each with 6 x RJ45 10 Gbps (Class E<sub>A</sub> pre-assembled with multi-cable, length: 2 m, GHMT-certified.

## Commercial data

Item number	1412898
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNMAY
GTIN	4046356967310
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

1412898

<https://www.phoenixcontact.com/us/products/1412898>

## Technical data

### Product properties

Type	19" rack patch module
Number of positions	48
Number of slots	6
Shielded	yes

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Transmission speed	10 Gbps

### Material specifications

Color	Bare metallic
Flammability rating according to UL 94	V0
Housing material	Stainless steel

### Cable/line

Shielded	yes
Cable type	Twisted pair
Cable type	Round cable
External cable diameter	18 mm ... 18 mm (AWG 23)
External cable diameter	18 mm ... 18 mm
External sheath, color	orange

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

1412898

<https://www.phoenixcontact.com/us/products/1412898>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)