

NBC-M12MS/20,0-94D/R4AC - Network cable



1412929

<https://www.phoenixcontact.com/us/products/1412929>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet, 8-pos., PVC, black RAL 9005, shielded, straight M12 plug, to RJ45, cable length: 20.0 m

Commercial data

Item number	1412929
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF19
Product key	AF1CMI
GTIN	4046356978187
Weight per piece (including packing)	1,041 g
Weight per piece (excluding packing)	1,007.2 g
Customs tariff number	85444290
Country of origin	US

1412929

<https://www.phoenixcontact.com/us/products/1412929>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	8
Coding	A

Interfaces

Bus system	Ethernet
Signal type/category	Ethernet

Electrical properties

Nominal voltage U_N	30 V AC
	30 V DC

Connector

Connection 1

Type	Plug straight M12 / IP67
Number of positions	8
Coding type	A (Standard)
Shielded	no
Handle color	black
Material	CuZn (Contact)
	Ni/Au (Contact surface)
	TPU GF (Contact carrier)
	TPU, hardly inflammable, self-extinguishing (Grip body)
	Stainless steel (Screw connection)
Insertion/withdrawal cycles	≥ 100
Insulation resistance	≥ 100 MΩ
Tightening torque	0.4 Nm
Degree of protection	IP67

Connection 2

Type	Plug straight RJ45 / IP20
Number of positions	8
Handle color	gray
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	PC (Contact carrier)
	PA (Housing)
Degree of protection	IP20

Cable/line

Cable length	20 m
--------------	------


NBC-M12MS/20,0-94D/R4AC - Network cable



1412929

<https://www.phoenixcontact.com/us/products/1412929>

Ethernet [94D]

Dimensional drawing	
UL AWM Style	2464 (80°C/300 V)
Number of positions	8
Shielded	yes
Cable type	Ethernet [94D]
Conductor structure	4x2xAWG26/7, SF/UTP
Signal speed	0.6 c
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	4x 2x 0.14 mm ²
Wire diameter incl. insulation	0.98 mm ±0.05 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PVC (reinforced) UV-resistant
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Thickness, outer sheath	0.80 mm
Twisted pairs	2 cores to the pair
Overall twist	4 pairs, twisted
Optical shield covering	85 %
Max. conductor resistance	< 140 Ω/km
Insulation resistance	≥ 5 GΩ*km
Wave impedance	100 Ω ±15 Ω (at 4 ... 100 MHz)
Cable capacity	< 56 nF/km
Nominal voltage, cable	72 V DC 300 V AC
Test voltage Core/Core	2500 V DC (2 s)
Test voltage Core/Shield	2500.00 V DC (2 s)
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm
Tensile strength	80 N
Flame resistance	According to VW-1
Resistance to oil	according to IEC 60811-2-1

NBC-M12MS/20,0-94D/R4AC - Network cable



1412929

<https://www.phoenixcontact.com/us/products/1412929>

Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (installation)	0 °C ... 50 °C

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP20

NBC-M12MS/20,0-94D/R4AC - Network cable



1412929

<https://www.phoenixcontact.com/us/products/1412929>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

1412929

<https://www.phoenixcontact.com/us/products/1412929>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com