

SACC-CIM12MSD4PL180THRSAMPLE - Contact carrier



1413550

<https://www.phoenixcontact.com/us/products/1413550>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system flush-type plug, Ethernet, 4-pos., D-coded, with straight THR solder connection, only contact insert

Commercial data

Item number	1413550
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABQAGM
GTIN	4055626008202
Weight per piece (including packing)	4.56 g
Weight per piece (excluding packing)	2.413 g
Country of origin	DE

SACC-CIM12MSD4PL180THRSAMPLE - Contact carrier



1413550

<https://www.phoenixcontact.com/us/products/1413550>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Data
Number of positions	4
Coding	D
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Rated surge voltage	2.5 kV
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U_N	250 V
Nominal current I_N	4 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Material specifications

Material Contact carrier	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM / EPDM
Flammability rating according to UL 94	V0

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	D

SACC-CIM12MSD4PL180THRSAMPLE - Contact carrier



1413550

<https://www.phoenixcontact.com/us/products/1413550>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
	-40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

SACC-CIM12MSD4PL180THRSAMPLE - Contact carrier




1413550

<https://www.phoenixcontact.com/us/products/1413550>

Drawings

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

SACC-CIM12MSD4PL180THRSAMPLE - Contact carrier




1413550

<https://www.phoenixcontact.com/us/products/1413550>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1413550>

 cULus Recognized Approval ID: E221474-20140616		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine					
		250 V	4 A	-	-

SACC-CIM12MSD4PL180THRSAMPLE - Contact carrier



1413550

<https://www.phoenixcontact.com/us/products/1413550>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CIM12MSD4PL180THRSAMPLE - Contact carrier



1413550

<https://www.phoenixcontact.com/us/products/1413550>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com