

SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Socket, M12-SPEEDCON, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Efficient PCB assembly: two-piece connectors for SMT soldering
- SPEEDCON fast locking system reduces cabling times

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1414023 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | AB23 |
| Product key | ABQBFC |
| GTIN | 4055626022659 |
| Weight per piece (including packing) | 9.2 g |
| Weight per piece (excluding packing) | 7.708 g |
| Customs tariff number | 79070000 |
| Country of origin | DE |

SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
| Order information: | Lock nut is included in the scope of delivery |

Product properties

| | |
|--------------|----------------------------|
| Product type | Circular connector housing |
| Thread type | M12 |

Connection data

| | |
|-------------------|--------------|
| Tightening torque | 1.5 ... 2 Nm |
|-------------------|--------------|

Material specifications

| | |
|-------------------------------|------------------------------|
| Material Housing | GD-Zn |
| Material Housing surface | nickel-plated |
| Seal material | FKM FKM |
| Material for screw connection | Zinc die-cast, nickel-plated |

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Socket |
| Head thread type | M12 |
| Head locking type | SPEEDCON |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection (when plugged in) | IP67 (correctly plugged in and locked) |
| Degree of protection | IP67 (correctly plugged in and locked) IP67, when in locked state |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation) |
| UL Type Rating | Type 4 (indoor use only) |

SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

Standards and regulations

| | |
|--------------------------|------------------------------|
| Standard designation | M12 circular connector |
| Standards/specifications | according to IEC 61076-2-101 |

Mounting

| | |
|---------------|---|
| Mounting type | Rear mounting (M15 x 1) |
| Assembly note | Spacing between the top edge of the PCB and the back of the front plate: 6 mm |

SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440224 |
| ECLASS-15.0 | 27440224 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003556 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31171600 |
|-------------|----------|

SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com