

SACC-SQ-M12MS-4CON-25F0,5-0,14 - Device connector front mounting



1414166

<https://www.phoenixcontact.com/us/products/1414166>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, 4-position, Pin, M12, A-coding, Individual wires, cable length: 0.5 m, 0.14 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239066

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1414166 |
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Product key | ABQCED |
| GTIN | 4055626017136 |
| Weight per piece (including packing) | 20.2 g |
| Weight per piece (excluding packing) | 18.261 g |
| Country of origin | DE |

SACC-SQ-M12MS-4CON-25F0,5-0,14 - Device connector front mounting



1414166

<https://www.phoenixcontact.com/us/products/1414166>

Technical data

Notes

Safety note

Safety note

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.

- WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

- The products are suitable for applications in plant, controller, and electrical device engineering.

- When operating the connectors in outdoor applications, they must be separately protected against environmental influences.

- Assembled products may not be manipulated or improperly opened.

- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).

- When using the product in direct connection with third-party manufacturers, the user is responsible.

- For operating voltages > 50 V AC, conductive connector housings must be grounded

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

- Observe the corresponding technical data. You will find information:

- o On the product
- o On the packing label
- o In the supplied documentation
- o Online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) under the product

- Only use tools recommended by Phoenix Contact

- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- The connector warms up in normal operation. Depending on the

SACC-SQ-M12MS-4CON-25F0,5-0,14 - Device connector front mounting



1414166

<https://www.phoenixcontact.com/us/products/1414166>

ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

| | |
|---------------------|-----------------------------------|
| Product type | Circular connectors (device side) |
| Number of positions | 4 |
| Coding | A |
| Thread type | M12 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Material specifications

| | |
|--------------------------|-----|
| Material wire insulation | TPE |
|--------------------------|-----|

Electrical properties

| | |
|-----------------------|-----------|
| Rated surge voltage | 2.5 kV AC |
| Nominal voltage U_N | 250 V |
| Nominal current I_N | 4 A |

Connection data

Conductor connection

| | |
|-------------------------|----------------------|
| Connection method | Individual wires |
| Contact connection type | Pin |
| Conductor cross-section | 0.14 mm ² |

Connector

Connection 1

| | |
|------------------|-----|
| Head design | Pin |
| Head thread type | M12 |
| Coding | A |

Cable/line

| | |
|---------------------|----------------------|
| Cable length | 0.5 m |
| Cable cross section | 0.14 mm ² |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -25 °C ... 85 °C |

SACC-SQ-M12MS-4CON-25F0,5-0,14 - Device connector front mounting



1414166

<https://www.phoenixcontact.com/us/products/1414166>

Standards and regulations

Standards/specifications

according to IEC 61076-2-101

SACC-SQ-M12MS-4CON-25F0,5-0,14 - Device connector front mounting



1414166

<https://www.phoenixcontact.com/us/products/1414166>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
|-------------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-SQ-M12MS-4CON-25F0,5-0,14 - Device connector front mounting



1414166

<https://www.phoenixcontact.com/us/products/1414166>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|--|--|

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | bbb94374-c367-4f53-8099-5b3b3ae41c5e |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com