

HC-B-TA-PG16-ER-AL - Adapter

1414261

<https://www.phoenixcontact.com/us/products/1414261>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter, aluminum, for EVO housing, Pg16 thread



Commercial data

Item number	1414261
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	AF7APM
GTIN	4055626022239
Weight per piece (including packing)	107.7 g
Weight per piece (excluding packing)	107.7 g
Customs tariff number	85389099
Country of origin	DE

HC-B-TA-PG16-ER-AL - Adapter

1414261

<https://www.phoenixcontact.com/us/products/1414261>

Technical data


Product properties

Product type	Thread adapter
Application	Bayonet B - Pg
Type of the screw connection	Pg16

Connection data

Tightening torque	... 7.5 Nm
-------------------	------------

Dimensions

Dimensional drawing	
Thread type on seal side	Pg16

Internal dimensions

Length of internal thread	13 mm
---------------------------	-------

Material specifications

Color	aluminum color
Material	Die-cast aluminum, corrosion-resistant
Seal material O-ring	NBR
Housing material	Die-cast aluminum, corrosion resistant

Cable/line

External cable diameter	depending on the cable gland
-------------------------	------------------------------

Mechanical properties

Mechanical data

Type of the screw connection	Pg16
------------------------------	------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

HC-B-TA-PG16-ER-AL - Adapter



1414261

<https://www.phoenixcontact.com/us/products/1414261>



Drawings

Dimensional drawing



Dimensional drawing

HC-B-TA-PG16-ER-AL - Adapter



1414261

<https://www.phoenixcontact.com/us/products/1414261>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414261>

DNV

Approval ID: TAE000037S



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-B-TA-PG16-ER-AL - Adapter



1414261

<https://www.phoenixcontact.com/us/products/1414261>

Classifications

ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

ETIM

ETIM 10.0	EC000441
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-B-TA-PG16-ER-AL - Adapter



1414261

<https://www.phoenixcontact.com/us/products/1414261>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com