

# HC-M-20-CT-F - Contact insert module



1414373

<https://www.phoenixcontact.com/us/products/1414373>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 20, power contacts: 20, control contacts: 0, Socket, Crimp connection, 690 V, 16 A, 0.5 mm<sup>2</sup> ... 4 mm<sup>2</sup>, application: Power

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1414373       |
| Packing unit                         | 2 pc          |
| Minimum order quantity               | 2 pc          |
| Sales key                            | BF62          |
| Product key                          | AF7ACE        |
| GTIN                                 | 4055626025261 |
| Weight per piece (including packing) | 22.6 g        |
| Weight per piece (excluding packing) | 22.6 g        |
| Customs tariff number                | 85389099      |
| Country of origin                    | PL            |

# HC-M-20-CT-F - Contact insert module



1414373

<https://www.phoenixcontact.com/us/products/1414373>

## Technical data

### Notes

|         |   |
|---------|---|
| General | For HEAVYCON housing type B6 to B48, HC-M-B...MF-... hinged module carrier frame required, CK2,5-ED... imp contacts, crimp contacts not supplied as standard. |
| General | Connectors may be operated only when there is no load/voltage.  |

### Mounting

|               |   |
|---------------|---|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
|---------------|---|

### Product properties

|                         |                        |
|-------------------------|------------------------|
| Product type            | Modular contact insert |
| Series                  | HC-M-20                |
| Application             | Power                  |
| Number of positions     | 20                     |
| Connection profile      | 20                     |
| Contact numbering       | 1 - 20                 |
| Number of module slots  | 2                      |
| No. of power contacts   | 20                     |
| No. of control contacts | 0                      |
| Contact material type   | turned                 |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Connection data


#### Connection technology

|                       |                  |
|-----------------------|------------------|
| Connection technology | Crimp connection |
|-----------------------|------------------|

#### Conductor connection

|   |   |
|---|---|
| Conductor cross-section                 | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
| Connection cross section AWG            | 20 ... 12                                 |
| Stripping length of the individual wire | 7.5 mm                                    |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 34.2 mm  |
| Height              | 39.95 mm   |

# HC-M-20-CT-F - Contact insert module



1414373

<https://www.phoenixcontact.com/us/products/1414373>

|        |         |
|--------|---------|
| Length | 29.4 mm |
|--------|---------|

## Mechanical characteristics

|                  |        |
|------------------|--------|
| Contact diameter | 2.5 mm |
|------------------|--------|

## Electrical properties

|                       |                |
|-----------------------|----------------|
| Rated voltage (III/3) | 690 V          |
| Rated surge voltage   | 6 kV           |
| Rated current         | 16 A           |
| SCCR                  | 5 kA (UL 2237) |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

## Material specifications

|  |                       |
|--|-----------------------|
| Flammability rating according to UL 94 | V0                    |
| Contact material                       | Copper alloy          |
| Contact surface material               | Ag (alternatively Au) |
| Contact carrier material               | PC                    |
| Standards/regulations                  | PC                    |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

## Standards and regulations

### Testing

|                       |   |
|-----------------------|---|
| Standards/regulations | PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
|-----------------------|---|

# HC-M-20-CT-F - Contact insert module





1414373

<https://www.phoenixcontact.com/us/products/1414373>


## Drawings

Dimensional drawing



Female insert


Schematic diagram



Connector pin assignment, connection side

1414373

<https://www.phoenixcontact.com/us/products/1414373>



Derating diagram

# HC-M-20-CT-F - Contact insert module



1414373

<https://www.phoenixcontact.com/us/products/1414373>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414373>

### DNV

Approval ID: TAE000037S



### CSA

Approval ID: 158887

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 600 V                 | 14 A                  | - 12              | -                           |



### UL Recognized

Approval ID: E118976

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 600 V                 | 17.5 A                | - 12              | -                           |



### UL Recognized

Approval ID: E468743

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 600 V                 | 17.5 A                | -                 | -                           |

# HC-M-20-CT-F - Contact insert module



1414373

<https://www.phoenixcontact.com/us/products/1414373>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440217 |
| ECLASS-15.0 | 27440217 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000438 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# HC-M-20-CT-F - Contact insert module



1414373

<https://www.phoenixcontact.com/us/products/1414373>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.113 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)