

# SAC-5P- 1,5-PVC/M12FR - Sensor/actuator cable



1415686

<https://www.phoenixcontact.com/us/products/1415686>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PVC, black RAL 9005, free cable end, on Socket angled M12, coding: A, cable length: 1.5 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1415686       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF03          |
| Product key                          | AF1CDA        |
| GTIN                                 | 4055626050478 |
| Weight per piece (including packing) | 72 g          |
| Weight per piece (excluding packing) | 71.7 g        |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

1415686

<https://www.phoenixcontact.com/us/products/1415686>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 5                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | HB  |
| Seal material                          | NBR   |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn  |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 48 V AC                    |
|                       | 60 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connector

#### Connection 1

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

#### Connection 2

|                     |                   |
|---------------------|-------------------|
| Type                | Socket angled M12 |
| Number of positions | 5                 |

# SAC-5P- 1,5-PVC/M12FR - Sensor/actuator cable



1415686

<https://www.phoenixcontact.com/us/products/1415686>

|             |   |
|-------------|---|
| Coding type | A |
|-------------|---|

## Cable/line

|              |       |
|--------------|-------|
| Cable length | 1.5 m |
|--------------|-------|

### PVC black [PVC]

|   |   |
|---|---|
| Dimensional drawing                           |               |
| Cable weight                                  | 51 kg/km  |
| UL AWM Style                                  | 2464 / 1729 (80°C/300 V)  |
| Number of positions                           | 5   |
| Shielded                                      | no  |
| Cable type                                    | PVC black [PVC]   |
| Conductor structure signal line               | 19x 0.15 mm   |
| AWG signal line                               | 22  |
| Conductor cross-section                       | 5x 0.34 mm <sup>2</sup> (Signal line)   |
| Wire diameter incl. insulation                | 1.26 mm ±0.05 mm  |
| External cable diameter                       | 5.00 mm ±0.15 mm  |
| Outer sheath, material                        | PVC   |
| External sheath, color                        | black RAL 9005  |
| Conductor material                            | Bare Cu litz wires  |
| Material wire insulation                      | PVC   |
| Single wire, color                            | brown, white, blue, black, green-yellow   |
| Thickness, insulation                         | ≥ 0.23 mm (Core insulation)   |
| Thickness, outer sheath                       | ≥ 0.76 mm   |
| Overall twist                                 | 5 wires around filler to the core   |
| Max. conductor resistance                     | max. 57 Ω/km (at 20 °C)   |
| Insulation resistance                         | ≥ 200 MΩ*km (at 20 °C)  |
| Nominal voltage, cable                        | ≤ 300 V   |
| Test voltage                                  | ≥ 3000 V  |
| Minimum bending radius, fixed installation    | 5 x D   |
| Minimum bending radius, flexible installation | 10 x D  |
| Smallest bending radius, fixed installation   | 25 mm   |
| Smallest bending radius, movable installation | 50 mm   |
| Flame resistance                              | UL VW-1   |
| Resistance to oil                             | in accordance with DIN EN 60811-2-1   |
| Ambient temperature (operation)               | -25 °C ... 80 °C (cable, fixed installation)<br>-10 °C ... 80 °C (Cable, flexible installation) |

# SAC-5P- 1,5-PVC/M12FR - Sensor/actuator cable



1415686

<https://www.phoenixcontact.com/us/products/1415686>

## Environmental and real-life conditions

### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Degree of protection  | IP65                             |
|   | IP67                             |
|   | IP68                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

# SAC-5P- 1,5-PVC/M12FR - Sensor/actuator cable

1415686

<https://www.phoenixcontact.com/us/products/1415686>




## Drawings

Dimensional drawing



M12 x 1 socket, angled

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SAC-5P- 1,5-PVC/M12FR - Sensor/actuator cable



1415686

<https://www.phoenixcontact.com/us/products/1415686>

Circuit diagram



Contact assignment of the M12 sockets

# SAC-5P- 1,5-PVC/M12FR - Sensor/actuator cable



1415686

<https://www.phoenixcontact.com/us/products/1415686>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415686>

|  <b>UL Listed</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 125 V                 | 4 A                   | -                 | -                           |

|  <b>cUL Listed</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 125 V                 | 4 A                   | -                 | -                           |

|  <b>EAC-RoHS</b><br>Approval ID: RU D-DE.HB35.B.00387 |  |  |  |  |
|--|--|--|--|--|
|--|--|--|--|--|

# SAC-5P- 1,5-PVC/M12FR - Sensor/actuator cable



1415686

<https://www.phoenixcontact.com/us/products/1415686>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-5P- 1,5-PVC/M12FR - Sensor/actuator cable



1415686

<https://www.phoenixcontact.com/us/products/1415686>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.655 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)