

SAC-5P-M12MSK/ 1,5-PUR PE - Power cable



1414866

<https://www.phoenixcontact.com/us/products/1414866>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 5-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: K, on free cable end, cable length: 1.5 m, for AC current up to 16 A/690 V, PE connection with Advanced Shielding Technology

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against mismatching, thanks to special K-coding
- Our standard: robust halogen-free PUR cable

Commercial data

Item number	1414866
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF05
Product key	AF1CDQ
GTIN	4055626034980
Weight per piece (including packing)	280 g
Weight per piece (excluding packing)	289.8 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P-M12MSK/ 1,5-PUR PE - Power cable



1414866

<https://www.phoenixcontact.com/us/products/1414866>

Technical data

Product properties

Product type	Power cable
Application	Energy supply
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	K

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Material of grip body	PP
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	690 V AC
Nominal current I_N	16 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Connector

Connection 1

Type	Plug straight M12
Coding type	K (Power)

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	1.5 m
--------------	-------


PUR halogen-free black [PUR]

SAC-5P-M12MSK/ 1,5-PUR PE - Power cable



1414866

<https://www.phoenixcontact.com/us/products/1414866>

Dimensional drawing	
Cable weight	165 kg/km
UL AWM Style	90 °C / 1000 V
Number of positions	5
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure, voltage supply	80x 0.20 mm
AWG power supply	14
Conductor cross-section	5x 2.5 mm ²
Wire diameter incl. insulation	2.8 mm ±0.1 mm
External cable diameter	9.00 mm ±0.3 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	black 1, black 2, black 3, black 4, green/yellow
Thickness, insulation	≥ 0.31 mm
Thickness, outer sheath	approx. 0.70 mm
Max. conductor resistance	≤ 8 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 1000 V AC
Test voltage	≥ 10000 V AC (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	45 mm
Smallest bending radius, movable installation	90 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥500000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815 in accordance with DIN EN 50267-2-1
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	according to DIN EN 60811-404, 168 h at 100 °C Hydrolysis and microbe resistant as per VDE 0282 section 10

SAC-5P-M12MSK/ 1,5-PUR PE - Power cable



1414866

<https://www.phoenixcontact.com/us/products/1414866>

Other resistance	Low adhesion
	abrasion-resistant
	Resistant to salt water
Ambient temperature (operation)	-50 °C ... 90 °C (cable, fixed installation)
	-30 °C ... 90 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67 (without preloading, as additional test in accordance with IEC 60529)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111

SAC-5P-M12MSK/ 1,5-PUR PE - Power cable

1414866

<https://www.phoenixcontact.com/us/products/1414866>

Drawings




Plug, M12 x 1, straight, shielded

Schematic diagram



Connector pin assignment of M12 plug, 5-pos., K-coded, pin side view



Contact assignment of the M12 plug

SAC-5P-M12MSK/ 1,5-PUR PE - Power cable





1414866


<https://www.phoenixcontact.com/us/products/1414866>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414866>

 UL Listed Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	16 A	- 14	- 14

 cUL Listed Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	16 A	- 14	-

 EAC-RoHS Approval ID: RU D-DE.HB35.B.00387				
--	--	--	--	--

SAC-5P-M12MSK/ 1,5-PUR PE - Power cable



1414866

<https://www.phoenixcontact.com/us/products/1414866>

Classifications

ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12MSK/ 1,5-PUR PE - Power cable



1414866

<https://www.phoenixcontact.com/us/products/1414866>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	3.006 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com